

SUPPLEMENTARY TERMS AND CONDITIONS

FOR THE 30-DAY MONEY BACK GUARANTEE

1. Agreement Terms

1.1 General Terms. These Supplementary Terms and Conditions for the 30-day Money Back Guarantee (“**MBG Supplementary Terms**”) apply to our limited Promotion on selected Instrument Products (defined below) provided by Life Technologies Corporation and its affiliates (individually, and collectively, referred to in these MBG Supplementary Terms as “**us**”, “**we**”, “**our**” or “**Thermo Fisher**”). These MBG Supplementary Terms are included as Supplementary Terms to the thermofisher.com Terms and Conditions of Sale (“**Terms and Conditions of Sale**”), available at www.thermofisher.com/legal and defined therein, and, together with our quotation, Documentation (defined below), and any other applicable Supplementary Terms, comprise the agreement (“**Agreement**”) between you and us for your purchase, and our sale of such Instrument Products. In the event of a conflict among the contract documents, the following order will apply as to the conflicting terms: the Documentation, other Supplementary Terms, these MBG Supplementary Terms, our quotation, and then the Terms and Conditions of Sale.

1.2 MBG Supplementary Terms Specific Definitions. For purposes of these MBG Supplementary Terms, the following definitions apply. All other capitalized terms have the meanings assigned in the Terms and Conditions of Sale.

“**Customer**” means the customer identified on the Thermo Fisher quotation for the supply of the Instrument Products, referred to in these MBG Supplementary Terms as “**you**”, “**your**”, or “**Customer**”.

“**Documentation**” means labels affixed to Instrument Products or packaging; documentation, specifications, limited use label licenses and/or accompanying package inserts shipped with Instrument Products; certificates of analysis or conformance made available for applicable Instrument Products; and/or documentation, specifications, use guidelines or instructions available in our catalogs, on our website, or that we provide to you for applicable Instrument Products.

“**Instrument Products**” means individually, and collectively, the products listed in the Exhibit.

“**Promotion**” means a thirty (30) day money-back guarantee under which the Customer may cancel the purchase and receive a full refund, without the need to provide any reason.

2. Scope

2.1 Applicability. This Promotion applies to Instrument Products purchased by Customer between January 05, 2026, and February 20, 2026, 5:00PM Eastern standard time, only. This Promotion applies to Customer’s in the United States (excluding Puerto Rico) or Canada only.

2.2 Qualification. New Customers will be required to complete and submit a quote demo form on our website, by selecting the online Promotion advertisement which will appear against the relevant Instrument Products. Existing Customers can opt-in for this Promotion via engagement with our existing sales channels and are not required to complete and submit a quote demo form.

2.3 Promotion Period. The promotion period commences upon (a) the date shipment of the Instrument Products is received where Customer’s own installation is applicable, or (b) upon the completion of training for the specified Instrument Products (iBright, Varioskan LUX and EVOS M7000 (“**Commencement Date**”), and continues for thirty (30) calendar days thereafter (“**Promotion Period**”).

2.4 Exercise. Customer can exercise its right to return the Instrument Products at any time during the Promotion Period, without reason or cause, provided that the return is initiated within the Promotion Period. For this purpose, initiated means that Customer has contacted Customer Services and instructed a return which has been authorized.

2.5 Exclusions. This offer does not apply to purchases made prior to the start of this offer. This Promotion does not apply to any Instrument Products which are returned to us (i) modified, enhanced or otherwise changed or supplemented; or (ii) damaged or tampered with. Reasonable wear and tear is permitted. Customers must return the Instrument Products in their original packaging and free of all security interests, liens and other encumbrances.

2.6 Training. If the Instrument Products purchased by Customer require training by us, or where such training is requested by Customer, and we cannot schedule that training within the Promotion Period, at our discretion we may permit Customer an additional period where it can exercise its right to return the Instrument Products under this Promotion. Such additional period shall be fourteen (14) calendar days from the date of such training.

3. Return Process

3.1 Returns. Upon Customer Services authorizing a return, we will either instruct our carrier to collect the Instrument Products from Customer or arrange for our team to attend Customer's premises to deinstall, re-package and remove the Instrument Products. For Instrument Products to be collected by our carrier, Customer shall deinstall, repackage and make the Instrument Products available for such collection on the date provided, or to follow any other written instructions provided by us.

3.2 Instructions. Customer must comply with any instructions provided by us in respect of return of the Instrument Products, including, where applicable, fully cleaning the Instrument Products, decontaminating the Instrument Products of radioactive, biological, toxic and other dangerous or hazardous materials or substances, and removing any data from the Instrument Products. If requested, Customer must complete and return a Certificate of Decontamination to us in this regard.

3.3 Costs. The costs of any return shall be borne by us.

4. Money Back

4.1 Inspection. Upon the return of the Instrument Products, we shall inspect the Instrument Products to ensure they are in compliance with Section 2.4 of these MBG Supplementary Terms.

4.2 Timeframe. Upon completion of the inspection, and our acceptance of the Instrument Products return, we shall, within sixty (60) days, initiate a refund to Customer of the purchase amount for the applicable Instrument Products. Such refund shall be processed to the method of payment used by Customer when purchasing the Instrument Products.

4.3 Deductions. There shall be no deductions made for the initial shipment, installation, training, or return costs associated with the Instrument Products under this Promotion. All such costs shall be borne by us.

4.4 Disputes. If we determine that Instrument Products for which you requested a return under this Promotion are not covered by the guarantee, any dispute by Customer of such determination shall be handled by Customer Services.

5. General

This Agreement constitutes the entire and exclusive agreement between the Parties with respect to your purchase and our sale of the Instrument Products and supersedes all prior representations, understandings or agreements, oral or written, between the Parties with respect to such subject matter. Headings are included herein for convenience of reference only and shall not constitute a part of the terms of this Agreement. This Agreement shall be governed by the laws of the Commonwealth of Massachusetts, exclusive of its conflicts of law provisions. For the avoidance of doubt, neither this Promotion, nor the terms and conditions of these MBG Supplementary Terms shall impact the application of Section 8.2 (Limited Warranties for Instruments) of our Terms and Conditions of Sale. We reserve the right to modify or withdraw these terms and conditions at any time.

EXHIBIT
INSTRUMENT PRODUCTS LIST

Thermo Fisher SKU number	Product Description
AMF3000	EVOS M3000 Imaging System
AMF3000S	EVOS M3000 Imaging System with Mechanical Stage
A40001411	EVOS M3000 Imaging System Extended Warranty Package
AMF5000	EVOS™ M5000 Imaging System
AMF5000SV	EVOS™ M5000 Imaging System
A65468	EVOS™ M5000 Imaging System Extended Warranty Package
AMF7000	EVOS™ M7000 Imaging System
A42844	EVOS™ M7000 Imaging System, Extended Warranty Package
AMF7000HCA	EVOS™ M7000 Imaging System, High-Content Analysis Package
AMF7000HCA3D	EVOS™ M7000 Imaging System, High-Content Analysis Package with 3D
IB31001	iBlot™ 3 Western Blot Transfer Device, 1 device
A56727	iBlot™ 3 Western Blot Transfer Device, with extended warranty, 1 device with warranty
A44240	iBright™ CL1500 Imaging System
A44114	iBright™ CL1500 Imaging System
A44240CFR	iBright™ CL1500 Imaging System
A44116	iBright™ CL750 Imaging System
A44241	iBright™ FL1500 Imaging System
A44115	iBright™ FL1500 Imaging System
A44241CFR	iBright™ FL1500 Imaging System
A51119600DPC	Multiskan SkyHigh with Touch Screen and μ Drop Duo Plate
A51119500C	Multiskan SkyHigh
A51119600C	Multiskan SkyHigh with Touch Screen
A51119700C	Multiskan SkyHigh with Touch Screen and Cuvette
A51119700DPC	Multiskan SkyHigh with Touch Screen, Cuvette, and μ Drop Duo Plate
NDEIGHT-LAPTOP	NanoDrop Eight Spectrophotometer with Laptop US/CAN
NDE-GL	NanoDrop Eight UV-Vis Spectrophotometer
NDEIGHT-E1PIP	NanoDrop Eight Spectrophotometer E1 ClipTip Bundle

NDEIGHT-PIP	NanoDrop Eight Spectrophotometer F1 ClipTip Bundle
NDLPLUSGL	NanoDrop Lite Plus Spectrophotometer
NDLPLUSPRGL	NanoDrop Lite Plus Spectrophotometer with Printer
NDULTRAGL	ND Ultra Microvolume Spec
NDULTRACGL	ND UltraC Microvolume Spec
NDULTRACFLGL	ND UltraC FL, Spec/Fluorometer
NDULTRAFLGL	ND Ultra FL, Spec/Fluorometer
VA000010C	Varioskan ALF
VL0000D0	Varioskan™ LUX Multimode Microplate Reader
VL0L00D0	Varioskan™ LUX Multimode Microplate Reader
VL0L0TD0	Varioskan™ LUX Multimode Microplate Reader
VLBL00GD0	Varioskan™ LUX Multimode Microplate Reader
VLBL00GD1	Varioskan™ LUX Multimode Microplate Reader
VLB000D0	Varioskan™ LUX Multimode Microplate Reader
VLBL00GD2	Varioskan™ LUX Multimode Microplate Reader
VLBL00D0	Varioskan™ LUX Multimode Microplate Reader
VLBL0TGD0	Varioskan™ LUX Multimode Microplate Reader
VLBL0TGD1	Varioskan™ LUX Multimode Microplate Reader
VLBLATD0	Varioskan™ LUX Multimode Microplate Reader
VLBL0TGD2	Varioskan™ LUX Multimode Microplate Reader
VLBLATGD0	Varioskan™ LUX Multimode Microplate Reader
VLBLATGD1	Varioskan™ LUX Multimode Microplate Reader
VLBLATGD2	Varioskan™ LUX Multimode Microplate Reader
VLBL00D1	Varioskan™ LUX Multimode Microplate Reader
VLBL0TD1	Varioskan™ LUX Multimode Microplate Reader
VLBLATD1	Varioskan™ LUX Multimode Microplate Reader
VLBL00D2	Varioskan™ LUX Multimode Microplate Reader
VLBL0TD2	Varioskan™ LUX Multimode Microplate Reader
VLBLATD2	Varioskan™ LUX Multimode Microplate Reader
VLBL0TD0	Varioskan™ LUX Multimode Microplate Reader