

# Supply Center requirements (Standard)

Specifications and more



## Storage space

### Freezer, fridge, and ambient

- Ambient, 4°C, and –20°C storage
- 3 in. clearance needed (sides, back, top)
- Dimensions (L x W x H) Exterior: 31 x 33 x 79 in.
- Floor plan (L x W): 40 x 130 in.



## Power

### Voltage

- 110 volts (USA/Canada)
- 220 volts (EMEA)
- 230 volts (Singapore)
- 240 volts (Australia)



## Connectivity

### Network configurations

- Ethernet or Wi-Fi
- Access to port 80, 443, 1194
- Consult with Thermo Fisher IT for more details

# Supply Center requirements (Express)

Specifications and more



## Storage space

### Freezer, fridge, and ambient

- Ambient, 4°C, and –20°C storage
- 3 in. clearance needed (sides, back, top)
- Dimensions (L x W x H) Exterior: 30 x 33 x 78 in.
- POS kiosk included with stand
- Floor plan (L x W): 40 x 130 in.



## Power Voltage

- 110 volts (USA/Canada)
- 220 volts (EMEA)
- 230 volts (Singapore)
- 240 volts (Australia)



## Connectivity Network configurations

- Ethernet or Wi-Fi
- Access to port 80, 443, 1194
- Consult with Thermo Fisher IT for more details

# Supply Center requirements (Premier)

## Specifications and more



### Storage space

#### Freezer, fridge, and ambient

- Ambient, 4°C, and -20°C storage
- 3 in. clearance needed (sides, back, top)
- Dimensions (L x W x H) Exterior: 32 x 30 x 79 in.
- [Click here for full specifications](#)
- Floor plan (L x W): 40 x 130 in.



### Power Voltage

- 110 volts (USA/Canada)
- 220 volts (EMEA)
- 230 volts (Singapore)
- 240 volts (Australia)



### Connectivity Network configurations

- Ethernet, Wi-Fi, ISP Provided Hotspot
- Access to port 80, 443, 1194
- Consult with Thermo Fisher IT for more details