

# Aeromonas Aminopeptidase Recombinant Protein, PeproTech®

## Product Details

Size	2 x 500 µg
Species	Bacteria
Expression system	E. coli
Amino acid sequence	MPPITQQATV TAWLPQVDAS QITGTISLE SFTNRFYTTT SGAQASDWIA SEWQALSASL PNASVKQVSH SGYNQKSVVM TITGSEAPDE WIVIGGHLDS TIGSHTNEQS VAPGADDDASGIAAVTEVIR VLSENNFPKP RSIAFMAYAA EEVGLRGSQD LANQYKSEGG NVVSALQLDM TNYKGSQADV VFITDYTDSN FTQYLTLMD EYLPSTLYGF DTCGYACSDH ASWHNAGYPAAMPFESKFND YNPRIHTTQD TLANSPTGS HAKKFTQLGL AYAIEMGSA T G
Molecular weight	31.4 kDa
Class	Recombinant
Type	Protein
Purity	98% by SDS-PAGE gel and HPLC analyses.
Endotoxin concentration	<1 EU/µg
Activity	Sequentially cleaves N-terminal amino acids except E, D, and X-P.
Conjugate	Unconjugated
Form	Lyophilized
Purification	HPLC, SDS-PAGE
Contains	no preservative
Storage conditions	-20°C

## Applications

## Tested Dilution

## Publications

Functional Assay (FN)

Assay-dependent

-

## Product Specific Information

100-10-1MG will be provided as 2 x 500 µg (100-10-500UG)

Recombinant Aeromonas Aminopeptidase is a 31.4 kDa protein containing 291 amino acid residues.

This product is shipped at ambient temperature. For storage, handling and reconstitution information, please see the lot-specific Certificate of Analysis

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.