Performance guarenteed'

ZO-2 Polyclonal Antibody


Product Details

Size	100 µg
Species Reactivity	Dog, Human, Mouse
Published Species	Dog, Rabbit, Pig, Rat, Sheep, Plant, Fish, Human, Mouse, Xenopus
Host/Isotype	Rabbit / IgG
Class	Polyclonal
Туре	Antibody
Conjugate	Unconjugated
Immunogen	Synthetic peptide derived from the central portion of the ZO-2 protein.
Form	Liquid
Concentration	0.25 mg/mL
Purification	Antigen affinity chromatography
Storage buffer	PBS, pH 7.4
Contains	0.1% sodium azide
Storage conditions	-20°C
RRID	AB_2533976

Applications	Tested Dilution	Publications
Western Blot (WB)	1-2 µg/mL	46 Publications
Immunohistochemistry (IHC)	Assay-dependent	17 Publications
Immunohistochemistry (Paraffin) (IHC (P))	-	2 Publications
Immunohistochemistry (PFA fixed) (IHC (PFA))	-	1 Publication
Immunohistochemistry (Frozen) (IHC (F))	-	3 Publications
Immunohistochemistry - Free Floating (IHC (Free))	-	1 Publication
Immunocytochemistry (ICC/IF)	1 μg/mL	31 Publications
Flow Cytometry (Flow)	-	1 Publication
ELISA (ELISA)	Assay-dependent	-
Immunoprecipitation (IP)	-	11 Publications
ChIP assay (ChIP)	-	1 Publication
GST Pull Down (GPD)	-	1 Publication
Miscellaneous PubMed (Misc)	-	5 Publications


Product Images For ZO-2 Polyclonal Antibody

1




ZO-2 Antibody (71-1400) in WB

Western blot analysis of ZO-2 was performed by loading 30 µg of HeLa (lane1), NIH\u0003T3 (lane2), MDCK (lane3), Caco-2 (lane4), A431 (lane5) and Hep G2 (lane6) cell lysate using Novex® NuPAGE® 4-12 % Bis-Tris gel (Product # NP0322BOX), XCell SureLock[™] Electrophoresis System (Product # El0002), Novex® Sharp Pre-Stained Protein Standard (LC5800), and Pierce[™] Power Blotter System (22834). Proteins were transferred to a nitrocellulose membrane and blocked with 5 % skim milk for 1 hour at room temperature. ZO-2 was detected at ~150 kDa using ZO-2 Rabbit Polyclonal Antibody (Product # 71-1400) at 1-2 µg/mL in 5 % skim milk at 4°C overnight on a rocking platform. Goat Anti-Rabbit IgG - HRP Secondary Antibody (G21234) at 1:5000 dilution was used and chemiluminescent detection was performed using Pierce[™] ECL Western Blotting Substrate (Product # 32106).



ZO-2 Antibody (71-1400) in ICC/IF

Immunofluorescent analysis of ZO2/TJP2 Antibody was done on 90% confluent log phase CaCo2 cells. The cells were fixed with 4% paraformaldehyde for 15 minutes, permeabilized with 0.25% Triton[™] X-100 for 10 minutes, and blocked with 5% BSA for 1 hour at room temperature. The cells were labeled with ZO2 /TJP2 Antibody (Product # 71-1400) at 1 µg/mL in 1% BSA and incubated for 3 hours at room temperature and then labeled with Alexa Fluor 488 Goat Anti-Rabbit IgG Secondary Antibody (Product # A-11008) at a dilution of 1:400 for 45 minutes at room temperature (Panel a: green). Nuclei (Panel b: blue) were stained with SlowFade® Gold Antifade Mountant with DAPI (Product # S36938). F-actin (Panel c: red) was stained with Alexa Fluor 594 Phalloidin (Product # A12381). Panel d is a merged image showing membrane localization. Panel e is a no primary antibody control. The images were captured at 40X magnification.



ZO-2 Antibody (71-1400) in WB

Western blot analysis of MDCK cells using Rabbit anti-ZO-2 polyclonal antibody (Product # 71-1400).

View more figures on thermofisher.com

□ 120 References

Western Blot (46)

Microbiome	Year			
Lactic acid from vaginal microbiota enhances cervicovaginal epithelial	2022			
barrier integrity by promoting tight junction protein expression.				
"Published figure using ZO-2 polyclonal antibody (Product # 71-1400) in Western Blot"				
Authors: Delgado-Diaz DJ,Jesaveluk B,Hayward JA,Tyssen D,Alisoltani A,Potgieter M,Bell L,Ross E,Iranzadeh A,Allali I, Dabee S,Barnabas S,Gamieldien H,Blackburn JM,Mulder N,Smith SB,Edwards VL,Burgener AD,Bekker LG,Ravel J, Passmore JS,Masson L,Hearps AC,Tachedjian G				
Frontiers in cellular and infection microbiology	Year 2022			
Aeromonas sobria Serine Protease Degrades Several Protein				
Components of Tight Junctions and Assists Bacterial Translocation				
Across the T84 Monolayer.				
"Published figure using ZO-2 polyclonal antibody (Product # 71-1400) in Western Blot"				
Authors: Ueda M,Kobayashi H,Seike S,Takahashi E,Okamoto K,Yamanaka H				
	ferences on thermofisher.con			
Immunohistochemistry (17)				
NPJ Regenerative medicine	Year			
ZO-2/Tjp2 suppresses Yap and Wwtr1/Taz-mediated hepatocyte to	2022			
cholangiocyte transdifferentiation in the mouse liver.				
"Published figure using ZO-2 polyclonal antibody (Product # 71-1400) in Immunohistochemistry"				
Authors: Xu J,Kausalya PJ,Ong AGM,Goh CMF,Mohamed Ali S,Hunziker W				
Circulation research	Year			
ZO-1 Regulates Intercalated Disc Composition and Atrioventricular Node	2020			
Conduction.	Species			
"71-1400 was used in Immunohistochemistry to determine the role of ZO-1 in cardiac function."				
Authors: Dai W,Nadadur RD,Brennan JA,Smith HL,Shen KM,Gadek M,Laforest B,Wang M,Gemel J,Li Y,Zhang J,Ziman				
BD,Yan J,Ai X,Beyer EC,Lakata EG,Kasthuri N,Efimov IR,Broman MT,Moskowitz IP,Shen L,Weber CR				
View more IHC ref	ferences on thermofisher.cor			
More applications with references on thermofisher.com				
IHC (P) (2) IHC (PFA) (1) IHC (F) (3) IHC (Free) (1) ICC/IF (31) Flow (1) IP (11)	ChIP (1)			
	····· (1)			
GPD (1) Misc (5)				
For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of si specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherw				
specifications and/or accompanying package inserts (Documentation), no cannot a standard in the standard in the standard provide interest is tailed only ment used of property family ment when the merely illustrative of the ge epresent that any Product will conform to such model or sample (inclusion). NO THER WARRANTIES, EXPRESS OR IMPLED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICL	eneral type and quality of goods and does not			
UYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS EFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESK	GNED, OR (IV) IMPROPER STORAGE AND			
ANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limita				