

IL5RA Monoclonal Antibody (26815), APC


Product Details	
Size	100 Tests
Species Reactivity	Human
Host/Isotype	Mouse / IgG1
Class	Monoclonal
Type	Antibody
Clone	26815
Conjugate	APC
Excitation/Emission Max	651/660 nm
Immunogen	Sf 21-derived recombinant human IL-5R alpha/CD125 Asp21-Arg335
Form	Liquid
Purification	Protein A/G
Storage buffer	Buffered saline solution with BSA
Contains	0.09% sodium azide
Storage conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_2608178

Applications	Tested Dilution	Publications
Flow Cytometry (Flow)	10 µL per million cells	-

Product Specific Information


In direct ELISAs and Western blots, this antibody does not cross-react with recombinant human (rh) IL-5 R beta, rhIL-9 R, rhIL-4 R, rmlIL-5 R alpha, or rhIL-13 R alpha 1.

Product Images For IL5RA Monoclonal Antibody (26815), APC




IL5RA Antibody (MA5-23581) in Flow

Flow cytometry of IL5RA in HEK293 human embryonic kidney cell line transfected with either (A) human IL5 R/CD125 or (B) irrelevant transfectants and eGFP. Samples were incubated in IL5RA monoclonal antibody (Product # MA5-23581). Quadrant markers were based on control antibody staining.



IL5RA Antibody (MA5-23581) in Flow

Flow cytometry of IL5RA in Human peripheral blood granulocytes. Samples were incubated in IL5RA monoclonal antibody (Product # MA5-23581) or isotype control.



For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.