

Normal Human Serum

Product Details	
Size	120 mg
Host/Isotype	Human / Ig
Class	Control
Type	Control
Conjugate	Unconjugated
Form	Lyophilized
Concentration	60.0 mg/mL
Storage buffer	PBS/whole serum, pH 7.6
Contains	0.05% sodium azide
Storage conditions	4° C
RRID	AB_2532169

Applications	Tested Dilution	Publications
Immunohistochemistry (IHC)	Assay-dependent	1 Publication
Immunocytochemistry (ICC/IF)	Assay-dependent	1 Publication
Control (Ctrl)	Assay-Dependent	-
Blocking Assay (BLOCK)	Assay-dependent	-

Product Specific Information

For blocking purposes, use 5% (v/v) solution (1:20 dilution from rehydrated volume). Rehydration according to instruction yields 100% serum.

Restoration and Storage: Store product at 4°C until opened. Restore with 2.0 mL distilled water. Centrifuge product if it is not completely clear after standing for 1-2 hours at room temperature. Product may be stored for up to several weeks at 4°C as an undiluted liquid. After dilution, do not use for more than one day. To extend the shelf-life of this product, freeze rehydrated undiluted product in small aliquots at -20°C.

Country of Origin: USA

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.