


# CD45R Monoclonal Antibody (RA3-6B2), PE-Cyanine7

Product Details	
Size	100 µg
Species Reactivity	Cat, Human, Mouse
Host/Isotype	Rat / IgG2a, kappa
Class	Monoclonal
Type	Antibody
Clone	RA3-6B2
Conjugate	PE-Cyanine7
Excitation/Emission Max	569/780 nm
Immunogen	exon A-specific epitope on CD45 from Abelson murine leukemia virus-induced pre-B cell lymphoma
Form	Liquid
Concentration	0.1 mg/mL
Purification	purified
Storage buffer	PBS with proprietary stabilizer
Contains	<0.1% sodium azide
Storage conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_2534412

Applications	Tested Dilution	Publications
Flow Cytometry (Flow)	0.2 µg/1x10 <sup>6</sup> cells	1 Publication

## Product Images For CD45R Monoclonal Antibody (RA3-6B2), PE-Cyanine7



**CD45R Antibody (A15398) in Flow**  
Flow cytometry analysis of CD45R in BALB/c mouse splenocytes. Cells were stained using CD45R Monoclonal Antibody (RA3-6B2), PE-Cyanine7 (Product # A15398) and Rat Anti-Mouse CD3ε-PE.

Flow Cytometry (1)

Mucosal immunology

Year  
2015

Reciprocal regulation of lymphoid tissue development in the large intestine by IL-25 and IL-23.

"A15398 was used in flow cytometry to assess IL-25 and IL-23 and reciprocal regulation of lymphoid tissue development in the large intestine"

Authors: Donaldson DS,Bradford BM,Artis D,Mabbott NA

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.