


CD35 Monoclonal Antibody (E11), Alexa Fluor 647

Product Details	
Size	100 Tests
Species Reactivity	Human
Host/Isotope	Mouse / IgG1
Class	Monoclonal
Type	Antibody
Clone	E11
Conjugate	Alexa Fluor® 647
Immunogen	Acute monocytic leukemia cells and normal blood monocytes
Form	Liquid
Concentration	0.04 mg/mL
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.4, with 1% BSA
Contains	0.0325% sodium azide
Storage Conditions	4° C, store in dark
RRID	AB_2633298


Applications	Tested	Dilution	Published
Flow Cytometry (Flow)	✓	5 µL/1x10 ⁶ cells	

Product Images For CD35 Monoclonal Antibody (E11), Alexa Fluor 647



CD35 Antibody (A51014) in Flow

Histogram plot of lymphocytes and monocytes from lysed whole blood cells stained for 20 minutes with CD35-Alexa Fluor® 647; x-axis: CD35-Alexa Fluor® 647 fluorescence, y-axis: count.



CD35 Antibody (A51014) in Flow

Scatter plot of lysed whole blood cells stained for 20 minutes with CD35-Alexa Fluor® 647; x-axis: CD35-Alexa Fluor® 647 fluorescence, y-axis: side scatter.

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.