

TNFR2 (soluble) Monoclonal Antibody (897C2G9)

Product Details	
Size	500 µg
Species Reactivity	Human
Published Species	Human
Host/Isotype	Mouse / IgG1
Class	Monoclonal
Type	Antibody
Clone	897C2G9
Conjugate	Unconjugated
Immunogen	Purified recombinant human soluble TNF Receptor II.
Form	Liquid
Concentration	1 mg/mL
Purification	Protein A
Storage buffer	PBS, pH 7.4
Contains	0.5mg/mL sodium azide
Storage conditions	4° C
RRID	AB_2536357

Applications	Tested Dilution	Publications
ELISA (ELISA)	Assay-dependent	2 Publications

Product Specific Information

This product is recommended as a capture antibody in Sandwich ELISA applications.

This clone can also be referred to as clone number 897C 2G9 1H3.

ELISA (2)

Journal of immunology (Baltimore, Md. : 1950)

Circulating immune complexes (IC) and IC-induced levels of GM-CSF are increased in sudanese patients with acute visceral Leishmania donovani infection undergoing sodium stibogluconate treatment: implications for disease pathogenesis.

Authors: Elshafie AI,Ahlin E,Mathsson L,EIghazali G,Rönnelid J

Year
2007

Species
Human

Gastroenterology

Role of tumor necrosis factor receptor 2 (TNFR2) in colonic epithelial hyperplasia and chronic intestinal inflammation in mice.

"AHR3022 was used in ELISA to determine the role of TNFR2 in chronic inflammation-induced colonic epithelial alteration."

Authors: Mizoguchi E,Mizoguchi A,Takedatsu H,Cario E,de Jong YP,Ooi CJ,Xavier RJ,Terhorst C,Podolsky DK,Bhan AK

Year
2002

Species
Human

Dilution
1 µg/ml

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.