

# SSEA1 Monoclonal Antibody (MC-480), DyLight 550

Product Details	
Size	100 µL
Species Reactivity	Human, Mouse
Host/Isotope	Mouse / IgM
Class	Monoclonal
Type	Antibody
Clone	MC-480
Conjugate	DyLight® 550
Immunogen	BALB/c mouse immunized with F9 teratocarcinoma stem cells (X-irradiated).
Form	Liquid
Concentration	1 mg/mL
Purification	Affinity chromatography - MBP
Storage buffer	PBS with proprietary stabilizer
Contains	0.02% sodium azide
Storage Conditions	4° C, do not freeze
RRID	AB_2536695

Applications	Tested	Dilution	Published
Flow Cytometry (Flow)	✓	1:50-1:500	


## Product Specific Information

MA1-022-D550 has been successfully used in flow cytometry on mouse and human samples.

## Product Images For SSEA1 Monoclonal Antibody (MC-480), DyLight 550

### SSEA1 Antibody (MA1-022-D550) in Flow

Flow cytometry analysis of SSEA-1 in F9 (red histogram) and NCCIT cells (orange histogram) compared to unstained cells (blue histogram). Positive staining is observed on F9 cells when compared to no antibody control (middle panel) and to SSEA-1-negative undifferentiated NCCIT cells (right panel). Cells were fixed with 2% paraformaldehyde and washed with PBS. Cells were blocked with 2% BSA-PBS for 30 minutes at room temperature and incubated with a DyLight 550-conjugated SSEA-1 monoclonal antibody (Product # MA1-022-D550) in 2% BSA-PBS at a dilution of 1:100 for 60 minutes at room temperature. Cells were washed and re-suspended in PBS for FACS analysis.



For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.