

# FPR2 Monoclonal Antibody (GM1D6)


Product Details	
Size	100 µg
Species Reactivity	Human
Host/Isotope	Mouse / IgG1, kappa
Class	Monoclonal
Type	Antibody
Clone	GM1D6
Conjugate	Unconjugated
Immunogen	cDNA encoding human FPRL1
Form	Liquid
Concentration	2 mg/mL
Purification	Protein G
Storage buffer	PBS, pH 7.2
Contains	no preservative
Storage Conditions	Store at 4°C short term. For long term storage, store at -20°C, avoiding freeze/thaw cycles.
RRID	AB_2105325

Applications	Tested	Dilution	Published
ELISA (ELISA)	✓	1:200-1:400	
Flow Cytometry (Flow)	✓	1.2 µg/1x10 <sup>6</sup> cells	
Immunocytochemistry (ICC)	✓	1 µg/1x10 <sup>6</sup> cells	
Immunofluorescence (IF)	✓	1 µg/1x10 <sup>6</sup> cells	

## Product Specific Information


This antibody recognizes native human FPRL1 protein expressed in transfected mammalian cells.

## Product Images For FPR2 Monoclonal Antibody (GM1D6)



### FPR2 Antibody (MA1-17769) in ICC

Immunocytochemistry analysis of CHO cells using Product # MA1-17769. CHO cells were transiently transfected with an expression vector encoding FPR1. Binding of Product # MA1-17769 was visualized with a FITC-conjugated secondary antibody (green). Actin filaments are labeled with Alexa Fluor-555 Phalloidin (red). Cell nuclei are stained with DAPI (blue).



### FPR2 Antibody (MA1-17769) in Flow

Flow cytometry analysis of FPR2 in BOSC23 cells using a FPR2 Monoclonal Antibody (Product # MA1-17769) at a 1.2  $\mu\text{g}/10^6$  cells dilution, detected with a PE-conjugated secondary antibody, as shown in red. Isotype control antibody is shown in black.

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.