


FAS Monoclonal Antibody (LT95), PE

Product Details	
Size	100 Tests
Species Reactivity	Human
Published Species	Mouse
Host/Isotype	Mouse / IgG1
Class	Monoclonal
Type	Antibody
Clone	LT95
Conjugate	PE
Excitation/Emission Max	565/576 nm
Immunogen	HUT-78 human T cell lymphoma cell line
Form	Liquid
Purification	Size-exclusion chromatography
Storage buffer	PBS, pH 7.4, with 0.2% BSA
Contains	15mM sodium azide
Storage conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_1955488

Applications	Tested Dilution	Publications
Flow Cytometry (Flow)	20 µL/ 1x10^6 cells	1 Publication

Product Images For FAS Monoclonal Antibody (LT95), PE



FAS Antibody (MA1-19795) in Flow
Flow cytometry analysis (surface staining) of human peripheral blood cells with anti-CD95 (LT95) PE Monoclonal antibody (Product # MA1-19795).

View more figures on thermofisher.com

Flow Cytometry (1)

Life science alliance	Year 2022
Mechanistic and pharmacodynamic studies of DuoBody-CD3x5T4 in preclinical tumor models.	Species Mouse
"MA1-19795 was used in Flow cytometry/Cell sorting to show in-depth mechanistic studies of a CD3 bsAb in solid cancer, using DuoBody-CD3x5T4."	
Authors: Kemper K,Gielen E,Boross P,Houtkamp M,Plantinga TS,de Poot SA,Burm SM,Janmaat ML,Koopman LA,van den Brink EN,Rademaker R,Verzijl D,Engelberts PJ,Satijn D,Sasser AK,Breij EC	

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (i) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (ii) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (iii) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (iv) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.