

Carboxypeptidase B2 Monoclonal Antibody (13H4)

Product Details	
Size	200 µg
Species Reactivity	Human
Published Species	Human
Host/Isotype	Mouse / IgG1
Class	Monoclonal
Type	Antibody
Clone	13H4
Conjugate	Unconjugated
Immunogen	Purified, full length, native human protein.
Form	Liquid
Concentration	3.5 mg/mL
Storage conditions	4° C, do not freeze
RRID	AB_779507

Applications	Tested Dilution	Publications
Western Blot (WB)	Assay-dependent	-
Immunohistochemistry (IHC)	-	1 Publication
ELISA (ELISA)	Assay-dependent	-
Affinity Purification (AP)	Assay-dependent	-

Product Specific Information

MA1-25767 detects Carboxypeptidase B2 from human samples.

Product Images For Carboxypeptidase B2 Monoclonal Antibody (13H4)



Carboxypeptidase B2 Antibody (MA1-25767) in WB
 Western blot analysis of Carboxypeptidase B2 using a Carboxypeptidase B2 monoclonal antibody (Product # MA1-25767) under non-reducing conditions.

Immunohistochemistry (1)

Histopathology	Year 2013
Value of -methylacyl-CoA racemase immunochemistry for predicting neoplastic progression in Barrett's oesophagus.	Species Human
"MA1-25767 was used in immunohistochemistry to study the predictive value of the immunohistochemical expression of alpha-methylacyl-CoA racemase in Barrett's oesophagus"	Dilution 1:200
Authors: Kastelein F,Biermann K,Steyerberg EW,Verheij J,Kalisvaart M,Looijenga LH,Stoop HA,Walter L,Kuipers EJ, Spaander MC,Bruno MJ	

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.