

PMA1 Monoclonal Antibody (40B7)

Product Details	
Size	250 µL
Species Reactivity	Yeast
Published Species	Yeast
Host/Isotype	Mouse / IgG
Class	Monoclonal
Type	Antibody
Clone	40B7
Conjugate	Unconjugated
Immunogen	Yeast membrane preps.
Form	Liquid
Concentration	Conc. Not Determined
Storage buffer	tissue culture supernatant
Contains	10mM sodium azide
Storage conditions	Store at 4°C short term. For long term storage, store at -20°C, avoiding freeze/thaw cycles.
RRID	AB_1959827

Applications	Tested Dilution	Publications
Western Blot (WB)	1:10,000	2 Publications
Immunocytochemistry (ICC/IF)	1:1,000-1:5,000	-

Product Specific Information

The predicted molecular weight by western blot is 100 kDa.

Western Blot (2)

Molecular medicine reports

Human apolipoprotein L1 interferes with mitochondrial function in *Saccharomyces cerevisiae*.

"MA1-91567 was used in Western Blotting to present evidence which suggests that APOL1 could be a physiological regulator of mitochondrial function."

Authors: Chidiac M,Daher J,Boeckstaens M,Poelvoorde P,Badran B,Marini AM,Khalaf R,Vanhamme L

Species
Yeast

Dilution
1:10000

Year
2020

Journal of receptor and signal transduction research

Identification of residues involved in homodimer formation located within a -strand region of the N-terminus of a Yeast G protein-coupled receptor.

"MA1-91567 was used in western blot to investigate the structure-function relationship of a yeast G protein-coupled receptor"

Authors: Uddin MS, Kim H, Deyo A, Naider F, Becker JM

Species
Yeast

Dilution
Not Cited

Year
2012

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.