

Phospho-BAD (Ser112) Monoclonal Antibody (G.445.9)


Product Details	
Size	100 µL
Species Reactivity	Human, Mouse, Non-human primate, Rat
Host/Isotope	Rabbit / IgG
Class	Monoclonal
Type	Antibody
Clone	G.445.9
Conjugate	Unconjugated
Immunogen	Synthetic phosphopeptide corresponding to residues surrounding pSer112 of mouse Bad
Form	Liquid
Purification	Affinity chromatography
Storage buffer	0.01M HEPES, pH 7.5, with 0.15M NaCl, 100µg/mL BSA, 50% glycerol
Contains	<0.02% sodium azide
Storage Conditions	-20°C
RRID	AB_10985837

Applications	Tested Dilution	Publications
Flow Cytometry (Flow)	1:800	-
Immunohistochemistry (Paraffin) (IHC (P))	1:50	-
Western Blot (WB)	1:1000	-

Product Specific Information


It is not recommended to aliquot this antibody.

Product Images For Phospho-BAD (Ser112) Monoclonal Antibody (G.445.9)




Phospho-BAD (Ser112) Antibody (MA5-15085) in IHC

Immunohistochemical analysis of Phospho-BAD pSer112 in paraffin-embedded COS cells, untreated (left) or TPA-treated (right), using a Phospho-BAD pSer112 monoclonal antibody (Product # MA5-15085) showing induced cytoplasmic staining.



Phospho-BAD (Ser112) Antibody (MA5-15085) in WB

Western blot analysis of Phospho-BAD pSer112 in extracts from COS cells, untreated or TPA-treated, using Phospho-BAD pSer112 monoclonal antibody (Product # MA5-15085) (upper) or a Bad polyclonal antibody (lower).



Phospho-BAD (Ser112) Antibody (MA5-15085) in WB

Western blot analysis of Phospho-BAD (Ser112) using a monoclonal antibody (Product # MA5-15085).

View more figures on thermofisher.com

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.