

Androgen Receptor Monoclonal Antibody (2H8)

Product Details	
Size	100 µL
Species Reactivity	Human
Host/Isotype	Mouse / IgG1
Class	Monoclonal
Type	Antibody
Clone	2H8
Conjugate	Unconjugated
Immunogen	Purified recombinant fragment of human AR expressed in E. Coli.
Form	Liquid
Concentration	Conc. Not Determined
Storage buffer	ascites
Contains	0.03% sodium azide
Storage Conditions	Store at 4°C short term. For long term storage, store at -20°C, avoiding freeze/thaw cycles.
RRID	AB_10985750

Applications	Tested Dilution	Publications
Western Blot (WB)	1/500 - 1/2000	-
Immunohistochemistry (IHC)	1/200 - 1/1000	-
ELISA (ELISA)	1:10,000	-

Product Specific Information


MA5-15598 targets Androgen receptor in IHC and WB applications and shows reactivity with Human samples.

The MA5-15598 immunogen is purified recombinant fragment of human AR expressed in E. Coli.


MA5-15598 detects Androgen receptor which has a predicted molecular weight of approximately 110kDa.

Androgen Receptor Antibody (MA5-15598)

Antibody specificity was demonstrated by detection of differential basal expression of the target across cell models owing to their inherent genetic constitution. Expression of Androgen Receptor was observed specifically in LNCaP using Anti-Androgen Receptor Monoclonal Antibody (2H8) (Product # MA5-15598) in Western Blot. Relative expression validation info.




Product Images For Androgen Receptor Monoclonal Antibody (2H8)



Androgen Receptor Antibody (MA5-15598) in IHC

Immunohistochemical analysis of paraffin-embedded human testis (left) and prostate cancer (right) tissues using Androgen receptor monoclonal antibody (Product # MA5-15598) followed with DAB staining.



Androgen Receptor Antibody (MA5-15598) in IHC

Immunohistochemical analysis of paraffin-embedded human prostate tissues using Androgen receptor monoclonal antibody (Product # MA5-15598).

[View more figures on thermofisher.com](https://www.thermofisher.com)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.