

MHC II Monomorphic Monoclonal Antibody (IL-A21), PE

Product Details


Size	100 Tests
Species Reactivity	Bovine
Host/Isotope	Mouse / IgG2a
Class	Monoclonal
Type	Antibody
Clone	IL-A21
Conjugate	PE
Form	Lyophilized
Concentration	1 mg/mL
Purification	Protein G
Storage buffer	PBS with 5% sucrose, 1% BSA
Contains	0.09% sodium azide
Storage Conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_2745454

Applications	Tested Dilution	Publications
Flow Cytometry (Flow)	Assay-dependent	-

Product Specific Information

Mouse anti Bovine MHC Class II Monomorphic antibody, clone IL-A21 recognizes a monomorphic epitope within the bovine MHC II cell surface antigen.

Product Images For MHC II Monomorphic Monoclonal Antibody (IL-A21), PE



MHC II Monomorphic Antibody (MA5-28494) in Flow

Flow cytometry of MHC II Monomorphic in bovine thymocytes. Sample was incubated in the presence of 10% bovine serum, MHC II Monomorphic monoclonal antibody (Product # MA5-28494) and gated on live, single cell thymocytes. Figures are arranged as follows: A) RPE conjugated Mouse anti Bovine CD1w2 Antibody and FITC conjugated Mouse IgG2a isotype control. B) RPE conjugated Mouse anti Bovine CD1w2 Antibody and FITC conjugated Mouse anti Bovine MHC Class II Monomorphic Antibody.

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.