

# CD5 Monoclonal Antibody (L17F12), DyLight™ 594


Product Details	
Size	100 Tests
Species Reactivity	Human
Host/Isotype	Mouse / IgG2a, kappa
Class	Monoclonal
Type	Antibody
Clone	L17F12
Conjugate	DyLight™ 594
Excitation/Emission Max	587/614 nm
Immunogen	Human acute lymphoblastic leukemia (ALL) T cells
Form	Liquid
Concentration	30 µg/mL
Purification	Size-exclusion chromatography
Storage buffer	PBS, pH 7.4, with 0.2% BSA
Contains	15mM sodium azide
Storage conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_2898651

Applications	Tested Dilution	Publications
Flow Cytometry (Flow)	4 µL/1x10^6 cells	-

## Product Specific Information


Do not use after expiration date stamped on vial label.

Product Images For CD5 Monoclonal Antibody (L17F12), DyLight™ 594



CD5 Antibody (MA5-38739) in Flow

Flow cytometry of CD5 in lymphocytes (red-filled) and neutrophil granulocytes (black-dashed). Samples were incubated with CD5 monoclonal antibody (Product # MA5-38739) followed by PE-DyLight 594 at a dilution of 4 µL reagent/100 µL of peripheral whole blood.



CD5 Antibody (MA5-38739) in Flow

Flow cytometry of CD5 in human peripheral whole blood. Samples were incubated with CD5 monoclonal antibody (Product # MA5-38739) followed by PE-DyLight 594 at a dilution of 4 µL reagent/100 µL of peripheral whole blood.

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (i) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (ii) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (iii) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (iv) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.