

CTR1 Polyclonal Antibody


Product Details	
Size	100 µL
Species	Human, Mouse, Pig, Rat, Xenopus, Zebrafish
Expression System	Rabbit / IgG
Class	Polyclonal
Type	Antibody
Conjugate	Unconjugated
Immunogen	Synthetic peptide of C-terminal region of human CTR1.
Form	Liquid
Concentration	1 mg/mL
Purification	Antigen affinity chromatography
Storage buffer	tris citrate/tris phosphate, pH 7-8
Contains	0.1% sodium azide
Storage Conditions	4° C, do not freeze
RRID	AB_568506

Applications	Tested Dilution	Publications
Immunocytochemistry (ICC)	1:500	-
Immunofluorescence (IF)	1:500	-
Immunohistochemistry (Frozen) (IHC (F))	Assay-Dependent	-
Immunohistochemistry (Paraffin) (IHC (P))	1:250	-

Product Specific Information


Suggested positive control: human breast cancer and kidney tissue.

Product Images For CTR1 Polyclonal Antibody



CTR1 Antibody (PA1-16586) in IHC

The photo on the left is antibody staining of hCTR1 overexpressing cell line. The photo on the right is antibody plus peptide competition staining.



CTR1 Antibody (PA1-16586) in IHC

Panel 1: human CTR1 staining of breast cancer tissue. Panel 2: human CTR1-antigen competition in breast cancer tissue.

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.