


Cyanine Polyclonal Antibody, AP

Product Details	
Size	100 µg
Species Reactivity	Chemical
Host/Isotype	Sheep / IgG
Class	Polyclonal
Type	Antibody
Conjugate	AP
Immunogen	Mixture of Cy3 and Cy5, conjugated KLH.
Form	Liquid
Concentration	1.4 mg/mL
Purification	IgG fraction
Storage buffer	0.05M tris HCl, pH 8.0, with 50% glycerol, 0.1mM ZnCl2, 1mM MgCl2, 10mg/mL BSA
Contains	0.01% sodium azide
Storage conditions	4° C, do not freeze
RRID	AB_779968

Applications	Tested Dilution	Publications
Western Blot (WB)	1:500-1:2,500	-
Immunohistochemistry (IHC)	1:200-1:1,000	-
ELISA (ELISA)	1:2,000-1:10,000	-

Product Specific Information
 PA1-26850 detects Cyanine.

Product Images For Cyanine Polyclonal Antibody, AP



Cyanine Antibody (PA1-26850) in WB

Western Blot using Cyanine Polyclonal Antibody, AP (Product # PA1-26850). Dot Blot of Sheep anti-Cyanine Antibody Alkaline Phosphatase Conjugated. Antigen: Row 1 - Cy3 Streptavidin Conjugated Row 2 - Cy5 Streptavidin Conjugated. Load: Lane 1 - 200 ng Lane 2 - 66.67 ng Lane 3 - 22.22 ng Lane 4 - 7.41 ng Lane 5 - 2.47 ng. Primary antibody: none. Secondary antibody: Cyanine Polyclonal Antibody, AP (Product # PA1-26850) at 1:1,000 for 60 min at RT.

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.