

iNOS Polyclonal Antibody

Product Details	
Size	7 mL
Published Species	Rat, Mouse
Host/Isotype	Rabbit / IgG
Class	Polyclonal
Type	Antibody
Conjugate	Unconjugated
Immunogen	Synthetic peptide derived from C-terminus of mouse i-NOS
Form	Liquid
Storage conditions	4° C, do not freeze
RRID	AB_1076179

Applications	Tested Dilution	Publications
Western Blot (WB)	-	1 Publication
Immunohistochemistry (Paraffin) (IHC (P))	Ready-to-use	-
Immunocytochemistry (ICC/IF)	-	1 Publication

Product Specific Information

Heat-mediated antigen retrieval is recommended prior to staining, using a 10mM citrate buffer, pH 6.0, for 10 minutes followed by cooling at room temperature for 20 min. Following antigen retrieval, incubate samples with primary antibody for 10 min at room temperature. A suggested positive control is lung tissue.

Western Blot (1)

<p>The British journal of dermatology</p> <p>Nicotine enhances skin necrosis and expression of inflammatory mediators in a rat pressure ulcer model.</p> <p>"PA1-37924 was used in western blot to study the role of nicotine in the development of pressure ulcers"</p> <p>Authors: Tsutakawa S,Kobayashi D,Kusama M,Moriya T,Nakahata N</p>	<p>Year</p> <p>2009</p> <p>Species</p> <p>Rat</p> <p>Dilution</p> <p>1:10</p>
--	--

Immunocytochemistry (1)

<p>Stem cells and development</p> <p>Comparison of osteogenic differentiation of embryonic stem cells and primary osteoblasts revealed by responses to IL-1, TNF-, and IFN-.</p> <p>"PA1-37924 was used in immunocytochemistry to study differences in the osteogenic differentiation of murine embryonic stem cells and murine primary osteoblasts"</p> <p>Authors: Sidney LE,Kirkham GR,Buttery LD</p>	<p>Year</p> <p>2014</p> <p>Species</p> <p>Mouse</p>
---	---

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.