

PSA Polyclonal Antibody

Product Details	
Size	1 mL
Published Species	Human
Host/Isotype	Rabbit / IgG
Class	Polyclonal
Type	Antibody
Conjugate	Unconjugated
Immunogen	Purified human PSA.
Form	Liquid
Concentration	8.75 mg/mL
Storage conditions	-20° C, Avoid Freeze/Thaw Cycles
RRID	AB_1086868

Applications	Tested Dilution	Publications
Western Blot (WB)	1:1,000	2 Publications
Immunohistochemistry (Paraffin) (IHC (P))	1:200	-
Immunocytochemistry (ICC/IF)	1:100	1 Publication

Product Specific Information

A suggested positive control is normal prostate or prostate carcinoma.

Western Blot (2)

<p>Andrologia</p> <p>Presence of PSA auto-antibodies in men with prostate abnormalities (prostate cancer/benign prostatic hyperplasia/prostatitis).</p> <p>"Published figure using PSA polyclonal antibody (Product # PA1-38514) in Western Blot"</p> <p>Authors: Lokant MT,Naz RK</p>	<p>Year 2015</p> <p>Species Human</p> <p>Dilution 1:5000</p>
<p>Journal of reproductive immunology</p> <p>Antibodies to prostate-specific antigen in immunoinfertile women and men.</p> <p>"PA1-38514 was used in western blot to study the incidence of antibodies against prostate specific antigen in the sera of immunoinfertile men and women"</p> <p>Authors: Naz RK,Butler TS</p>	<p>Year 2013</p> <p>Species Human</p>

Immunocytochemistry (1)

<p>Biosensors & bioelectronics</p> <p>Immunodevice for simultaneous detection of two relevant tumor markers based on separation of different microparticles by dielectrophoresis.</p> <p>"PA1-38514 was used in immunocytochemistry to develop a simultaneous detection method for tumor markers alpha-fetoprotein and prostate-specific antigen"</p> <p>Authors: Ramón-Azcón J,Yasukawa T,Mizutani F</p>	<p>Year 2011</p> <p>Species Human</p> <p>Dilution 1-10 µg/mL</p>
--	--

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.