

PODXL Polyclonal Antibody

Product Details	
Size	100 µL
Species Reactivity	Human, Mouse
Host/Isotype	Rabbit / IgG
Class	Polyclonal
Type	Antibody
Conjugate	Unconjugated
Immunogen	Human Podocalyxin protein.
Form	Liquid
Concentration	0.90 mg/mL
Purification	Antigen affinity chromatography
Storage buffer	tris glycine with 0.15M NaCl
Contains	0.05% sodium azide
Storage Conditions	-20° C, Avoid Freeze/Thaw Cycles
RRID	AB_2237224

Applications	Tested Dilution	Publications
Flow Cytometry (Flow)	1:100	-
Immunocytochemistry (ICC)	1:1000	1 Publication
Immunofluorescence (IF)	1:1000	1 Publication
Western Blot (WB)	2 µg/mL	-

Product Specific Information


This immunogen should be sufficiently distant from any glycosylation site.

Suggested positive control: human lung protein.

Product Images For PODXL Polyclonal Antibody


PODXL Antibody (PA1-46169) in WB

Western Blot detection of podocalyxin in human lung lysate



PODXL Antibody (PA1-46169) in Flow

FACS staining of NTERA-2 cells using Product # PA1-46169 at a 1:50 dilution detected using Dylight-488 conjugated goat anti-rabbit IgG secondary antibody.



[View more figures on thermofisher.com](https://www.thermofisher.com)

Immunocytochemistry (1)

Journal of mammary gland biology and neoplasia

Polarized Secretion of Extracellular Vesicles by Mammary Epithelia.

"Published figure using PODXL polyclonal antibody (Product # PA1-46169) in Immunofluorescence"

Authors: Chin AR, Yan W, Cao M, Liu X, Wang SE

Species
Not Applicable

Dilution
Not Cited

Year
2018

Immunofluorescence (1)

Journal of mammary gland biology and neoplasia

Polarized Secretion of Extracellular Vesicles by Mammary Epithelia.

"Published figure using PODXL polyclonal antibody (Product # PA1-46169) in Immunofluorescence"

Authors: Chin AR, Yan W, Cao M, Liu X, Wang SE

Species
Not Applicable

Dilution
Not Cited

Year
2018

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.