

# NFκB p105 Polyclonal Antibody

## Product Details

Size	100 μL
Species Reactivity	Bovine, Human, Mink, Mouse, Non-human primate, Pig, Rat
Host/Isotype	Rabbit / IgG
Class	Polyclonal
Type	Antibody
Conjugate	Unconjugated
Immunogen	Synthetic peptide corresponding to amino acids at the carboxy-terminus of human NFκB1 p105
Form	Liquid
Purification	Antigen affinity chromatography
Storage buffer	0.01M HEPES, pH 7.5, with 0.15M NaCl, 100μg/mL BSA, 50% glycerol
Contains	no preservative
Storage conditions	-20°C
RRID	AB_10983940


Applications	Tested Dilution	Publications
Western Blot (WB)	1:1,000	1 Publication
Immunoprecipitation (IP)	1:50	-

## Product Specific Information

It is not recommended to aliquot this antibody.

This antibody is not cross-reactive with the p50 subunit or other NF-κB family members.

## Product Images For NFκB p105 Polyclonal Antibody



### NFκB p105 Antibody (PA5-17150) in WB

Western blot analysis of NF-kappa-B1 p105 in extracts from THP-1 cells, differentiated with TPA (80 nM for 24 h) and treated with 1 µg/mL LPS, using NF-kappa-B1 p105 polyclonal antibody (Product # PA5-17150).

## 1 Reference

### Western Blot (1)

Nature communications

#### A central role of IKK2 and TPL2 in JNK activation and viral B-cell transformation.

"Published figure using NFκB p105 polyclonal antibody (Product # PA5-17150) in Western Blot"

Authors: Voigt S, Sterz KR, Giehler F, Mohr AW, Wilson JB, Moosmann A, Kieser A

**Species**  
Not Applicable

**Dilution**  
Not Cited

**Year**  
2020

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.