


# Complement Factor B Polyclonal Antibody

| Product Details    |                                                                                                   |
|--------------------|---------------------------------------------------------------------------------------------------|
| Size               | 400 µL                                                                                            |
| Species Reactivity | Human                                                                                             |
| Host/Isotype       | Rabbit / IgG                                                                                      |
| Class              | Polyclonal                                                                                        |
| Type               | Antibody                                                                                          |
| Conjugate          | Unconjugated                                                                                      |
| Immunogen          | KLH conjugated synthetic peptide between 469-494 amino acids from the central region of human CFB |
| Form               | Liquid                                                                                            |
| Concentration      | 0.5 mg/mL                                                                                         |
| Purification       | Protein A, Antigen affinity chromatography                                                        |
| Storage buffer     | PBS                                                                                               |
| Contains           | 0.09% sodium azide                                                                                |
| Storage conditions | -20° C, Avoid Freeze/Thaw Cycles                                                                  |
| RRID               | AB_2543547                                                                                        |

| Applications                              | Tested Dilution | Publications |
|-------------------------------------------|-----------------|--------------|
| Western Blot (WB)                         | 1:1,000         | -            |
| Immunohistochemistry (Paraffin) (IHC (P)) | 1:50-1:100      | -            |
| Flow Cytometry (Flow)                     | 1:10-1:50       | -            |


## Product Images For Complement Factor B Polyclonal Antibody



**Complement Factor B Antibody (PA5-26047) in IHC (P)**  
Immunohistochemistry analysis in formalin-fixed, paraffin-embedded human skeletal muscle using a CFB polyclonal antibody (Product # PA5-26047), followed by HRP-conjugated secondary antibody and DAB staining.


### Complement Factor B Antibody (PA5-26047) in WB

Western blot analysis using a CFB polyclonal antibody (Product # PA5-26047) in mouse kidney tissue lysates (35 µg per lane).



### Complement Factor B Antibody (PA5-26047) in Flow

Flow cytometry analysis of 293 cells using a CFB polyclonal antibody (Product # PA5-26047) (right) compared to a negative control cell (left) at a dilution of 1:10-50, followed by a FITC-conjugated goat anti-rabbit antibody



For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (i) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (ii) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (iii) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (iv) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.