

# ACOT8 Polyclonal Antibody

| Product Details    |                                                                                              |
|--------------------|----------------------------------------------------------------------------------------------|
| Size               | 100 µL                                                                                       |
| Species Reactivity | Human, Mouse, Rat                                                                            |
| Host/Isotype       | Rabbit / IgG                                                                                 |
| Class              | Polyclonal                                                                                   |
| Type               | Antibody                                                                                     |
| Conjugate          | Unconjugated                                                                                 |
| Immunogen          | Recombinant fragment corresponding to a region within amino acids 42 and 304 of Human ACOT8  |
| Form               | Liquid                                                                                       |
| Concentration      | 1 mg/mL                                                                                      |
| Purification       | Antigen affinity chromatography                                                              |
| Storage buffer     | 0.1M tris glycine, pH 7, with 10% glycerol                                                   |
| Contains           | 0.01% thimerosal                                                                             |
| Storage conditions | Store at 4°C short term. For long term storage, store at -20°C, avoiding freeze/thaw cycles. |
| RRID               | AB_2545449                                                                                   |

| Applications      | Tested Dilution | Publications |
|-------------------|-----------------|--------------|
| Western Blot (WB) | 1:500-1:3,000   | -            |

## Product Specific Information

Recommended positive controls: 293T, HepG2, Molt-4, Raji, mouse liver, rat liver.


Predicted reactivity: Mouse (83%), Rat (84%), Rhesus Monkey (97%), Bovine (83%).

Store product as a concentrated solution. Centrifuge briefly prior to opening the vial.

## Product Images For ACOT8 Polyclonal Antibody


### ACOT8 Antibody (PA5-27973) in WB

Western Blot using ACOT8 Polyclonal Antibody (Product # PA5-27973). Sample (30 µg whole cell lysate). A: MOLT4. Lane B: Raji. 10% SDS PAGE. ACOT8 Polyclonal Antibody (Product # PA5-27973) diluted at 1:1,000.




### ACOT8 Antibody (PA5-27973) in WB

ACOT8 antibody detects ACOT8 protein by western blot analysis. Various whole cell extracts (30 µg) were separated by 10% SDS-PAGE, and the membrane was blotted with ACOT8 antibody ACOT8 Polyclonal Antibody (Product # PA5-27973) diluted by 1:1,000.



### ACOT8 Antibody (PA5-27973) in WB

ACOT8 antibody detects ACOT8 protein by western blot analysis. Mouse tissue extracts (50 µg) was separated by 10 % SDS-PAGE, and the membrane was blotted with ACOT8 antibody ACOT8 Polyclonal Antibody (Product # PA5-27973) diluted by 1:1,000.



[View more figures on thermofisher.com](https://thermofisher.com)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (i) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (ii) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (iii) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (iv) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.