


STRA8 Polyclonal Antibody

Product Details	
Size	400 µL
Species Reactivity	Human
Published Species	Human
Host/Isotype	Rabbit / IgG
Class	Polyclonal
Type	Antibody
Conjugate	Unconjugated
Immunogen	KLH conjugated synthetic peptide between 286-315 amino acids from the C-terminal region of human STRA8
Form	Liquid
Concentration	0.5 mg/mL
Purification	Protein A, Antigen affinity chromatography
Storage buffer	PBS
Contains	0.09% sodium azide
Storage Conditions	-20° C, Avoid Freeze/Thaw Cycles
RRID	AB_2552357

Applications	Tested Dilution	Publications
Immunohistochemistry (Paraffin) (IHC (P))	1:10-1:50	-
Western Blot (WB)	1:2000	-
Immunocytochemistry (ICC)	-	1 Publication

Product Images For STRA8 Polyclonal Antibody




STRA8 Antibody (PA5-35047) in IHC (P)

Immunohistochemistry analysis of STRA8 in formalin-fixed, paraffin-embedded human testis tissue using a STRA8 polyclonal antibody (Product # PA5-35047) followed by peroxidase conjugation of the secondary antibody and DAB staining.

STRA8 Antibody (PA5-35047) in WB

Western blot analysis of STRA8 in 293 cell lysate (35 µg/lane) using a STRA8 polyclonal antibody (Product # PA5-35047).



Immunocytochemistry (1)

The Journal of clinical investigation

Zika virus infects human testicular tissue and germ cells.

"PA5-35047 was used in Immunocytochemistry-immunofluorescence to provide insights into how ZIKV may persist in semen and alter semen parameters, as well as a valuable tool for testing antiviral agents."

Authors: Matusali G,Houzet L,Satie AP,Mahé D,Aubry F,Couderc T,Frouard J,Bourgeau S,Bensalah K,Lavoué S, Jogue G,Bujan L,Cabié A,Avelar G,Lecuit M,Le Tortorec A,Dejuçq-Rainsford N

Species
Human

Dilution
Not Cited

Year
2018

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.