


CaMKII alpha/beta/delta Polyclonal Antibody

Product Details	
Size	100 µg
Species Reactivity	Human, Mouse, Rat
Published Species	Mouse
Host/Isotype	Rabbit / IgG
Class	Polyclonal
Type	Antibody
Conjugate	Unconjugated
Immunogen	A synthetic peptide derived from the internal region of human CaMK2 alpha/beta/sigma
Form	Liquid
Concentration	1 mg/mL
Storage conditions	-20°C
RRID	AB_2554841

Applications	Tested Dilution	Publications
Immunohistochemistry (IHC)	-	3 Publications
Immunohistochemistry (Paraffin) (IHC (P))	1:50-1:100	-

Product Images For CaMKII alpha/beta/delta Polyclonal Antibody



CaMKII alpha/beta/delta Antibody (PA5-38239) in IHC (P)
 Immunohistochemical analysis of CaM Kinase II alpha + beta + delta in paraffin-embedded human brain tissue using a CaM Kinase II alpha + beta + delta polyclonal antibody (Product # PA5-38239).

Immunohistochemistry (3)

Frontiers in cellular neuroscience	Year 2020
Methodological Approach for Optogenetic Manipulation of Neonatal Neuronal Networks.	
"Published figure using CaMKII alpha/beta/delta polyclonal antibody (Product # PA5-38239) in Immunofluorescence"	
Authors: Bitzenhofer SH,Ahlbeck J,Hanganu-Opatz IL	
Neuron	Year 2020
Resolving and Rescuing Developmental Miswiring in a Mouse Model of Cognitive Impairment.	Species Mouse
"PA5-38239 was used in Immunohistochemistry to report that pyramidal neurons in superficial layers of the prefrontal cortex are key elements causing disorganized oscillatory entrainment of local circuits in beta-gamma frequencies."	Dilution 1:200
Authors: Chini M,Pöpplau JA,Lindemann C,Carol-Perdiguer L,Hnida M,Oberländer V,Xu X,Ahlbeck J,Bitzenhofer SH, Mulert C,Hanganu-Opatz IL	

[View more IHC references on thermofisher.com](#)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (i) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (ii) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (iii) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (iv) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.