

Adenosine Deaminase Polyclonal Antibody


Product Details	
Size	100 µL
Species Reactivity	Human
Host/Isotope	Rabbit / IgG
Class	Polyclonal
Type	Antibody
Conjugate	Unconjugated
Immunogen	A synthetic peptide corresponding to the C-terminus of the Human Adenosine Deaminase/ADA
Form	Liquid
Purification	Protein A, Antigen affinity chromatography
Storage buffer	PBS
Contains	0.03% Proclin 300
Storage Conditions	Maintain refrigerated at 2-8°C for up to 1 month. For long term storage store at -20°C

Applications	Tested	Dilution	Published
Immunohistochemistry (Paraffin) (IHC (P))	✓	1:500-1:3000	
Immunoprecipitation (IP)	✓	1-5µL/mg of lysate	
Western Blot (WB)	✓	1:500-1:2000	

Product Specific Information


This antibody has specificity for Human Adenosine Deaminase/ADA.

Product Images For Adenosine Deaminase Polyclonal Antibody




Adenosine Deaminase Antibody (PA5-80316) in IHC (P)

Immunohistochemical staining of human ADA in human duodenum with Adenosine Deaminase Polyclonal Antibody (Product # PA5-80316) (1:2000, formalin-fixed paraffin embedded sections).



Adenosine Deaminase Antibody (PA5-80316) in IHC (P)

Immunohistochemical staining of human ADA in human brain with Adenosine Deaminase Polyclonal Antibody (Product # PA5-80316) (1:2000, formalin-fixed paraffin embedded sections).



Adenosine Deaminase Antibody (PA5-80316) in WB

Western blot analysis of Adenosine Deaminase in Lane A: Jurkat Whole Cell Lysate (30 μ g). Samples were probed using a Adenosine Deaminase Polyclonal Antibody (Product # PA5-80316) at a 1:500 dilution, followed by a Goat Anti-Rabbit IgG (H+L), HRP Secondary Antibody at a 1:10000 dilution. Western blot was performed under reducing conditions. Predicted band size:41 kDa.

[View more figures on thermofisher.com](https://www.thermofisher.com)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.