

Human BMP-2 Recombinant Protein

Product Details

Size	100 µg
Species	Human
Expression system	E. coli
Amino acid sequence	QAKHKQRKRL KSSCKRHPLY VDFSVDGWND WIVAPPGYHA FYCHGECFPF LADHLNSTNH AIVQTLVNSV NSKIPKACCV PTELSAISML YLDENEKVVL KNYQDMVVEG CGCR
Molecular weight	25 kDa
Class	Recombinant
Type	Protein
Purity	>95% by SDS-PAGE
Endotoxin concentration	<0.1 ng/µg
Activity	ED50 < 1.0 µg/mL; determined by the dose-dependent induction of alkaline phosphatase in mouse ATDC52 chondrogenic cells.
Conjugate	Unconjugated
Form	Lyophilized
Purification	sequential chromatography
Contains	no preservative
Storage conditions	4° C

Applications	Tested Dilution	Publications
Western Blot (WB)	Assay-dependent	-
Immunohistochemistry (IHC)	Assay-dependent	-
ELISA (ELISA)	Assay-dependent	-
Functional Assay (FN)	Assay-dependent	-
Control (Ctrl)	Assay-dependent	-

Product Specific Information

Carrier-Free

Reconstitution: Centrifuge the vial briefly, before opening to bring the contents to the bottom. Reconstitute the lyophilized protein in sterile 20 mM acetic acid to a concentration of 0.1-1.0 mg/mL. Apportion the reconstituted protein into working aliquots and store at -20°C. Make any further dilutions of the reconstituted protein in low endotoxin medium or a buffered solution containing a carrier protein such as heat inactivated FCS or tissue culture grade BSA.

Storage: Store the lyophilized protein at 2-8°C or -2°C for long term storage, preferably desiccated. Upon reconstitution, apportion into working aliquots and store at -20°C. Avoid repeated freeze-thaw cycles.

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.

