

Human HIPK3 (YAK1), His Tag Recombinant Protein

Product Details	
Size	10 µg
Species	Human
Expression system	Insect cells
Amino acid sequence	163-562
Tag	His-tag
Molecular weight	49.7 kDa
Class	Recombinant
Type	Protein
Conjugate	Unconjugated
Form	Liquid
Concentration	See Label
Purification	purified
Storage buffer	50mM tris HCl, pH 7.5, with 150mM NaCl, 0.02% Triton X-100, 50% glycerol, 2mM DTT, 0.5mM EDTA
Contains	no preservative
Storage conditions	-80° C, Avoid Freeze/Thaw Cycles

Applications	Tested Dilution	Publications
Kinase Assay (KA)	Assay-dependent	-

Product Specific Information

For maximum recovery please spin prior to use. Unless noted below, aliquots of the 5 µg, 10 µg and 20 µg sizes of kinase are not recommended as materials can be used in original packaging until exhausted. For larger sizes, the number of freeze/thaws may be reduced by preparing aliquots, aliquots below 20 µL are not recommended. Please never store a kinase diluted. If properly stored at -80C, this product is guaranteed for 6 months from date of purchase.

Protein Form: Catalytic

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.