

# Rabbit anti-Goat IgG F(ab')<sub>2</sub> Secondary Antibody, Biotin

Product Details	
Size	1.5 mL
Species Reactivity	Goat
Host/Isotype	Rabbit / IgG
Class	Polyclonal
Type	Secondary Antibody
Conjugate	Biotin
Form	Lyophilized
Concentration	1.4 mg/mL
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.6, with 15mg/mL BSA
Contains	0.05% sodium azide
Storage conditions	4° C
RRID	AB_228399

Applications	Tested Dilution	Publications
Western Blot (WB)	1:20,000-1:400,000	-
Immunohistochemistry (IHC)	1:500-1:5,000	-
Immunocytochemistry (ICC/IF)	1:500-1:5,000	-
Flow Cytometry (Flow)	1:200-1:1,000	-
ELISA (ELISA)	1:20,000-1:400,000	-
Immunoprecipitation (IP)	1:500-1:5,000	-

## Product Specific Information

Concentration may vary slightly from lot-to-lot, see lot-specific datasheet for exact concentration.

Product # 31753 has been successfully used in Western blot, IF, ICC, IHC, IP and FACS applications.

Product # 31753 reacts with the light chains of goat IgG and with the light chains common to most goat immunoglobulins, but not with the Fc portion of goat IgG or with non-immunoglobulin serum proteins. However, this antibody may cross-react with immunoglobulins from other species.

Store product at 4°C until opened. To extend the shelf-life of this product, add an equal volume of glycerol to make a final concentration of approximately 50% glycerol and store at -20°C.

Reconstitute with 1.5 mL of distilled water (1.4 mg/mL after restoration, lot-dependent).

Country of Origin: USA

### The disintegrin domain of ADAM9: a ligand for multiple beta1 renal integrins. Biochem J (2005)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.