

# Mouse anti-Human IgG1 Fc Secondary Antibody, Biotin

Product Details	
Size	250 µL
Host/Isotype	Mouse / IgG1
Class	Monoclonal
Type	Secondary Antibody
Clone	HP6069
Conjugate	Biotin
Immunogen	IgG gamma 1
Form	liquid
Concentration	1 mg/mL
Storage conditions	4° C
RRID	AB_2534052

Applications	Tested Dilution	Publications
Immunocytochemistry (ICC/IF)	1-10 µg/mL	-
Flow Cytometry (Flow)	-	0 Publication
ELISA (ELISA)	-	0 Publication

## Product Specific Information

This product is conjugated to biotin via a long linker.

## 5 References

IgG subclasses as biomarkers for persistence of factor VIII inhibitors in previously untreated patients with severe haemophilia A. Br J Haematol (2021)

Boosting of Markers of Fc Receptor Function in Anti-HIV Antibodies During Structured Treatment Interruption. AIDS Res Hum Retroviruses (2019)

Survey of the anti-factor IX immunoglobulin profiles in patients with hemophilia B using a fluorescence-based immunoassay. J Thromb Haemost (2016)

Characterization of the anti-factor VIII immunoglobulin profile in patients with hemophilia A by use of a fluorescence-based immunoassay. J Thromb Haemost (2015)

Severity and phenotype of bullous pemphigoid relate to autoantibody profile against the NH<sub>2</sub>- and COOH-terminal regions of the BP180 ectodomain. J Invest Dermatol (2002)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (i) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (ii) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (iii) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (iv) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.