

# Goat anti-Mouse IgG (H+L) Cross-Adsorbed Secondary Antibody, FITC

Product Details	
Size	2 mg
Species Reactivity	Mouse
Host/Isotope	Goat / IgG
Class	Polyclonal
Type	Secondary Antibody
Conjugate	FITC
Immunogen	Gamma Immunoglobins Heavy and Light chains
Form	Liquid
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2, with 1% BSA
Contains	0.05% sodium azide
Storage Conditions	Store at 4°C short term. For long term storage, store at -20°C, avoiding freeze/thaw cycles. Store in the dark.
RRID	AB_2534746

Applications	Tested Dilution	Publications
Flow Cytometry (Flow)	1:500-1:20,000	1 Publication
Immunofluorescence (IF)	1:500-1:20,000	-

## 1 Reference

### Flow Cytometry (1)

Journal of immunology (Baltimore, Md. : 1950)

#### Critical Differences between Induced and Spontaneous Mouse Models of Graves' Disease with Implications for Antigen-Specific Immunotherapy in Humans.

"A16073 was used in flow cytometry to investigate the use of thyrotropin receptor A to treat induced and spontaneous mouse models of Graves' disease"

Authors: Rapoport B, Banuelos B, Aliesky HA, Hartwig Trier N, McLachlan SM

**Species**  
Not Applicable

**Dilution**  
Not Cited

**Year**  
2016

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.