

CD3/CD8/CD45 Antibody Cocktail, FITC, PE, PE-Cyanine5

Catalog NumberMA1-12472

Product data sheet

Details		Species Reactivity	
Size	50 Tests	Species reactivity	Human
Host/Isotope	Mouse / IgG1	<div>Tested ApplicationsDilution * Flow Cytometry (Flow)Assay-dependent</div>	
Class	Cocktail		
Type	Antibody	<div>* Suggested working dilutions are given as a guide only. It is recommended that the user titrate the product for use in their own experiment using appropriate negative and positive controls.</div>	
Clone	M2AB, 17D8, BHPT-1		
Immunogen	human thymocytes, human peripheral blood T lymphocytes and peripheral blood monocytes from a rheumatoid arthritis patient		
Conjugate	FITC , PE , PE-Cyanine5		
Form	Liquid		
Storage Conditions	4° C, store in dark, DO NOT FREEZE!		

Product specific information

This antibody is a monoclonal mixture of FITC-conjugated CD3 (clone M2AB, isotype IgG1), PE-conjugated CD8 (clone 17D8, isotype IgG1) and Cy5-PE-conjugated CD45 (clone BHPT-1, isotype IgG1).

Background/Target Information

Triple color combination consisting of FITC, R-PE and PE-Cy5 conjugated monoclonal antibodies mixed in optimal ratio.

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization.

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization.

Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample.

NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (i) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (ii) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (iii) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (iv) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.