



GPR37L1 Polyclonal Antibody

Catalog Number PA5-33704

Product data sheet

Details		Tested Applications		Dilution *	
Size	50 µg	Immunohistochemistry (Paraffin) (IHC (P))	4-7 µg/mL	* Suggested working dilutions are given as a guide only. It is recommended that the user titrate the product for use in their own experiment using appropriate negative and positive controls.	
Host/Isotope	Rabbit / IgG				
Class	Polyclonal				
Type	Antibody				
Immunogen	Synthetic 17 amino acid peptide from 3rd cytoplasmic domain of human GPR37L1.				
Conjugate	Unconjugated				
Form	Liquid				
Concentration	1 mg/mL				
Storage Conditions	Maintain refrigerated at 2-8°C for up to 1 month. For long term storage store at -20°C				

Product specific information

Percent identity with other species by BLAST analysis: Human, Gorilla, Gibbon, Monkey (100%) Marmoset, Mouse, Rat, Hamster, Elephant, Panda, Dog, Horse (94%) Bovine (88%).

Background/Target Information

This polyclonal antibody was raised in Rabbit against GPR37L1. This antibody is unconjugated. This antibody is useful for testing in the following assays: IHC-P. The specificity of this antibody has been described as follows: Human GPR37L1. BLAST analysis of the peptide immunogen showed no homology with other human proteins.

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization.

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization.

Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample.

NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (i) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (ii) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (iii) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (iv) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.