IL-1 beta Antibody Cocktail

Product Details	
Size	500 µg
Species Reactivity	Human
Published Species	Human, Mouse
Host/Isotype	Mouse / IgG1, kappa
Class	Cocktail
Type	Antibody
Clone	508A4A2 and 508A7G8
Conjugate	Unconjugated
Immunogen	Recombinant human IL-1b
Form	Liquid
Concentration	1 mg/mL
Purification	Protein A
Storage buffer	PBS, pH 7.4
Contains	0.5mg/mL sodium azide
Storage conditions	4° C
RRID	AB_2536253

Applications	Tested Dilution	Publications
ELISA (ELISA)	Assay-dependent	3 Publications

Product Specific Information

This clone can also be referred to as clone number 508A 7G8 R1/508A 4A2 L2.

3 References

ELISA (3)

Journal of immunology (Baltimore, Md. : 1950)

Caspase activity is required for stimulated B lymphocytes to enter the cell cycle.

"AHC0612 was used in ELISA to study how caspase-6 regulates the cell cycle of tonsillar B cells."

Authors: Olson NE,Graves JD,Shu GL,Ryan EJ,Clark EA

Year
2003

Species
Human

Endocrinology

Igf-I inhibits spontaneous apoptosis in human granulocytes.

"AHC0612 was used in ELISA to examine the effects of IGF-I on in vitro apoptosis of human peripheral blood granulocytes."

Authors: Kooijman R,Coppens A,Hooghe-Peters E

Year
2002

Species
Human

Dilution
1 µg/ml

View more ELISA references on thermofisher.com

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.