

# CD54 (ICAM-1) Monoclonal Antibody (HA58), PE, eBioscience™

## Product Details

Size	100 Tests
Species Reactivity	Human
Published Species	Human, Mouse
Host/Isotype	Mouse / IgG1, kappa
Recommended Isotype Control	Mouse IgG1 kappa Isotype Control (P3.6.2.8.1), PE, eBioscience™
Class	Monoclonal
Type	Antibody
Clone	HA58
Conjugate	PE
Excitation/Emission Max	565/576 nm
Form	Liquid
Concentration	5 µL/Test
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2, with 0.2% BSA
Contains	0.09% sodium azide
Storage conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_10598517

Applications	Tested Dilution	Publications
Flow Cytometry (Flow)	5 µL (0.25 µg)/test	23 Publications
Miscellaneous PubMed (Misc)	-	1 Publication

## Product Specific Information


**Description:** The HA58 monoclonal antibody reacts with human CD54 (InterCellular Adhesion Molecule-1, ICAM-1), a 90-110 kDa transmembrane glycoprotein expressed by monocytes, lymphocytes and endothelial cells. Expression of CD54 is upregulated on activated lymphocytes. Interaction of CD54 with its ligand CD11a is important in the inflammatory response.

**Applications Reported:** The HA58 antibody has been reported for use in flow cytometric analysis.

**Applications Tested:** The HA58 antibody has been pre-titrated and tested by flow cytometric analysis of normal human peripheral blood cells. This can be used at 5 µL (0.25 µg) per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10<sup>5</sup> to 10<sup>8</sup> cells/test.


**Excitation:** 488-561 nm; **Emission:** 578 nm; **Laser:** Blue Laser, Green Laser, Yellow-Green Laser.

**Filtration:** 0.2 µm post-manufacturing filtered.




**CD54 (ICAM-1) Antibody (12-0549-42)**

Antibody clone (HA58) specificity was demonstrated by CRISPR-Cas9 mediated knockout of target protein. Loss of signal was observed for target protein in CD54 KO cells (blue histogram) compared to the control Cas9 cells (pink histogram) using CD54 antibody (HA58) (Product # 12-0549-42). Yellow histogram represents staining with the isotype control. {KO}



**CD54 (ICAM-1) Antibody (12-0549-42) in Flow**

Knockout of ICAM-1 (CD54) was achieved by CRISPR-Cas9 genome editing using LentiArray™ Lentiviral sgRNA (Product # A32042, Assay ID CRISPR845355\_LV) and LentiArray Cas9 Lentivirus (Product # A32064). Flow cytometry analysis of CD54 was performed by staining Raji CD54 Knock out cells with 0.25 µg Mouse IgG1 kappa Isotype Control (P3.6.2.8.1), PE, eBioscience™ (Product # 12-4714-82, yellow histogram) or 0.25 µg CD19 Monoclonal Antibody (HIB19), PE, eBioscience™ (Product # 12-0549-42, blue histogram). Raji Cas9 control cells were also stained with 0.25 µg CD19 Monoclonal Antibody (HIB19), PE, eBioscience™ (Product # 12-0549-42, pink histogram). Loss of signal was observed in the CD54 KO cells stained with CD54 antibody clone HA58 but not in the control Cas9 cells. Fixable Viability Dye eFluor780 (Product # 65-0865-18) was used for staining and selecting viable cells for analysis.



**CD54 (ICAM-1) Antibody (12-0549-42)**

Antibody clone (HA58) specificity was demonstrated by CRISPR-Cas9 mediated knockout of target protein. Loss of signal was observed for target protein in CD54 KO cells (blue histogram) compared to the control Cas9 cells (pink histogram) using CD54 antibody (HA58). Yellow histogram represents staining with the isotype control. {KO}

View more figures on [thermofisher.com](https://thermofisher.com)

Flow Cytometry (23)

<p>PLoS genetics</p> <p><b>Multimodal CRISPR perturbations of GWAS loci associated with coronary artery disease in vascular endothelial cells.</b></p> <p>"Published figure using CD54 (ICAM-1) monoclonal antibody (Product # 12-0549-42) in Flow Cytometry"</p> <p>Authors: Wünnemann F,Fotsing Tadjó T,Beaudoin M,Lalonde S,Lo KS,Kleinstiver BP,Lettre G</p>	<p>Year</p> <p>2023</p>
<p>Immunity, inflammation and disease</p> <p><b>Impact of latency-reversing agents on human macrophage physiology.</b></p> <p>"Published figure using CD54 (ICAM-1) monoclonal antibody (Product # 12-0549-42) in Flow Cytometry"</p> <p>Authors: Hany L,Turmel MO,Barat C,Ouellet M,Tremblay MJ</p>	<p>Year</p> <p>2023</p>

[View more Flow references on thermofisher.com](#)

Miscellaneous PubMed (1)

<p>Biophysical journal</p> <p><b>Minimal encounter time and separation determine ligand-receptor binding in cell adhesion.</b></p> <p>"12-0549-42 was used in bead preparation to probe the hidden kinetics of ligand-receptor bond formation using single-molecule flow chamber assays and Brownian dynamics simulations."</p> <p>Authors: Robert P,Nicolas A,Aranda-Espinoza S,Bongrand P,Limozin L</p>	<p>Year</p> <p>2011</p> <p>Species</p> <p>Human</p>
---	---

More applications with references on thermofisher.com

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.