

Goat anti-Human IgG (H+L) Cross-Adsorbed Secondary Antibody, HRP

Product Details	
Size	1 mg
Species Reactivity	Human
Host/Isotype	Goat / IgG
Class	Polyclonal
Type	Secondary Antibody
Conjugate	HRP
Immunogen	Gamma Immunoglobins Heavy and Light chains
Form	Lyophilized
Concentration	1 mg/mL
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2, with 1% BSA
Contains	0.1% ProClin 150
Storage conditions	Store at 4°C short term. For long term storage, store at -20°C, avoiding freeze/thaw cycles.
RRID	AB_2535588

Applications	Tested Dilution	Publications
Western Blot (WB)	1:500-1:20,000	0 Publication
Immunohistochemistry (IHC)	1:500-1:20,000	-
ELISA (ELISA)	1:500-1:20,000	-
Miscellaneous PubMed (Misc)	-	0 Publication


Product Specific Information

Rehydrate with 1.1 mL of deionized water and let stand 30 minutes at room temperature to dissolve. (Product has been overfilled to ensure complete recovery.) Centrifuge to remove any particulates. Prepare fresh working dilution daily. Store lyophilized material at 2-8 °C. For long term storage after reconstitution, dilute with 50% glycerol and store at -20 °C as a liquid. Based on Immunoelectrophoresis, no reactivity is observed to: non-immunoglobulin human serum immunoglobulins, serum proteins from bovine, mouse or rabbit.

Product Images For Goat anti-Human IgG (H+L) Cross-Adsorbed Secondary Antibody, HRP


Human IgG (H+L) Cross-Adsorbed Secondary Antibody (A18811) in WB

Western blot (non-reducing) was performed using Goat anti-Human IgG (H+L) Cross-Adsorbed Secondary Antibody, HRP (Product # A18811) and a 150 kDa band corresponding to Human IgG was observed in IM-9, ARH-77 and IM-9, ARH-77 conditioned medium8203 (CM) but not in Raji, Molt-4, Jurkat and Jurkat CM which are known to have low expression. Whole cell lysate (30 µg) of Raji (Lane 1), MOLT-4 (Lane 2), Jurkat (Lane 3), IM-9 (Lane 4), ARH-77 (Lane 5), IM-9 CM (Lane 6), ARH-77 CM (Lane 7) and Jurkat CM (Lane 8) were electrophoresed using NuPAGE™ 4-12% Bis-Tris Protein Gel (Product # NP0322BOX). Resolved proteins were transferred onto a nitrocellulose membrane (Product # IB23001) by iBlot® 2 Dry Blotting System (Product # IB21001). The blot was probed with Goat anti-Human IgG (H+L) Cross-Adsorbed Secondary Antibody, HRP (Product # A18811) (1:2000 dilution) and detected by chemiluminescence using iBright FL1500 (Product # A44115). Chemiluminescentdetection was performed using Novex® ECL Chemiluminescent Substrate Reagent Kit (Product # WP20005). IM-9 and ARH-77 express and secrete IgG whereas Raji is known to express IgM. MOLT-4 and Jurkat (T-cell lines) do not express immunoglobulins (DOI:10.1002/eji.1830100305;10.3791/3573;10.1016/0022-1759(94)00286-6;PMID: 566614).



Human IgG (H+L) Cross-Adsorbed Secondary Antibody (A18811) in WB

Western blot was performed using Goat anti-Human IgG (H+L) Cross-Adsorbed Secondary Antibody, HRP (Product # A18811) and ~55 kDa and ~25 kDa bands corresponding to Human IgG Heavy and Light Chain respectively was observed in Human IgG but not in IgA, IgE, IgM, Mouse IgG, Mouse IgM and Rabbit IgG (Panel I). Purified protein (100 ng) of Human IgG (Lane 1), IgA (Lane 2), IgE (Lane 3), IgM (Lane 4), Mouse IgG (Lane 5), Mouse IgM (Lane 6) and Rabbit IgG (Lane 7) were electrophoresed using NuPAGE™ 4-12% Bis-Tris Protein Gel (Product # NP0322BOX). Resolved proteins were then transferred onto a nitrocellulose membrane (Product # IB23001) by iBlot® 2 Dry Blotting System (Product # IB21001). The blot was probed with Goat anti-Human IgG (H+L) Cross-Adsorbed Secondary Antibody, HRP (Product # A18811) (1:2000 dilution) and detected using the iBright FL1500 (Product # A44115). Chemiluminescent detection was performed using Novex® ECL Chemiluminescent Substrate Reagent Kit (Product # WP20005). Silver staining was performed to establish equivalent loading of purified proteins using the Pierce™ Silver Stain Kit (Product # 24612) (Panel II). A band corresponding to BSA (*) which is part of the Mouse IgM formulation can be seen at ~60 kDa.



35 References

Safety and immunogenicity of a booster dose of S-268019-b: Interim findings of a Phase 3, open-label clinical study in Japan. Vaccine X (2023)

Determination of seroprevalence and kinetics of humoral response using mpox virus A29 protein. Commun Med (Lond) (2023)

Plasma cells in human pancreatic ductal adenocarcinoma secrete antibodies against self-antigens. JCI Insight (2023)

B-Cell Epitopes-Based Chimeric Protein from SARS-CoV-2 N and S Proteins Is Recognized by Specific Antibodies in Serum and Urine Samples from Patients. Viruses (2023)

Self-assembling SARS-CoV-2 spike-HBsAg nanoparticles elicit potent and durable neutralizing antibody responses via genetic delivery. NPJ Vaccines (2023)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (i) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (ii) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (iii) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (iv) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.