

# LIN28A Polyclonal Antibody

Product Details	
Size	100 µL
Species Reactivity	Human, Mouse, Pig
Host/Isotype	Rabbit / IgG
Class	Polyclonal
Type	Antibody
Conjugate	Unconjugated
Immunogen	Recombinant protein encompassing a sequence within the center region of human LIN28.
Form	Liquid
Concentration	1 mg/mL
Purification	Antigen affinity chromatography
Storage buffer	PBS, pH 7, with 1% BSA, 20% glycerol
Contains	0.01% thimerosal
Storage conditions	Store at 4°C short term. For long term storage, store at -20°C, avoiding freeze/thaw cycles.
RRID	AB_2792617

Applications	Tested Dilution	Publications
Western Blot (WB)	1:500-1:10,000	-
Immunohistochemistry (Paraffin) (IHC (P))	1:100-1:1,000	-
Flow Cytometry (Flow)	1:50-1:200	-

## Product Specific Information

Keep as concentrated solution.

Predicted reactivity: Mouse (98%), Rat (98%), Cat (96%), Pig (96%), Chicken (82%), Sheep (98%), Bovine (96%).



Positive Control: human ESC, mouse ESC, pig heart tissue.

Store product as a concentrated solution. Centrifuge briefly prior to opening the vial.

Product Images For LIN28A Polyclonal Antibody


LIN28A Antibody (PA5-85477) in Flow

Flow cytometry analysis of LIN28A in human embryonic stem cells using LIN28A polyclonal antibody (Product # PA5-85477) at a dilution of 1:100. Sample was then incubated with rabbit IgG (black) secondary antibody.



LIN28A Antibody (PA5-85477) in IHC (P)

Immunohistochemical analysis of paraffin-embedded human gastric cancer, using LIN28A Polyclonal Antibody (Product # PA5-85477) antibody at 1:500 dilution. Antigen Retrieval: EDTA based buffer, pH 8.0, 15 min.



LIN28A Antibody (PA5-85477) in IHC (P)

Immunohistochemistry analysis of LIN28A in paraffin-embedded human gastric cancer tissue using LIN28A polyclonal antibody (Product # PA5-85477) at a dilution of 1:500.

[View more figures on thermofisher.com](https://thermofisher.com)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (i) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (ii) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (iii) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (iv) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.