

AGTR1 Polyclonal Antibody

Product Details	
Size	100 µg
Species Reactivity	Human, Mouse
Published Species	Mouse
Host/Isotype	Goat / IgG
Class	Polyclonal
Type	Antibody
Conjugate	Unconjugated
Immunogen	Synthetic peptide sequence (EIQKNKPRNDDIFK) corresponding to the internal amino acids of AGTR1
Form	Liquid
Concentration	0.5 mg/mL
Purification	Ammonium sulfate precipitation
Storage buffer	TBS, pH 7.3, with 0.5% BSA
Contains	0.02% sodium azide
Storage conditions	-20° C, Avoid Freeze/Thaw Cycles
RRID	AB_10982239

Applications	Tested Dilution	Publications
Western Blot (WB)	0.1-0.3 µg/mL	1 Publication
Immunohistochemistry (Paraffin) (IHC (P))	-	1 Publication

Product Specific Information

This antibody is tested in Peptide ELISA: antibody detection limit dilution 32,000.

Product Images For AGTR1 Polyclonal Antibody

