

# CD243 (ABCB1) Monoclonal Antibody (UIC2), FITC, eBioscience™

Product Details	
Size	100 Tests
Species Reactivity	Human
Published Species	Human
Host/Isotype	Mouse / IgG2a, kappa
Recommended Isotype Control	Mouse IgG2a kappa Isotype Control (eBM2a), FITC, eBioscience™
Class	Monoclonal
Type	Antibody
Clone	UIC2
Conjugate	FITC
Form	Liquid
Concentration	5 µL/Test
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2, with 0.1% gelatin, 0.2% BSA
Contains	0.09% sodium azide
Storage conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_11220266

Applications	Tested Dilution	Publications
Flow Cytometry (Flow)	5 µL (0.5 µg)/test	1 Publication

## Product Specific Information

Description: This monoclonal antibody reacts with human Multidrug Resistant (MDR)-1, which is also known as P-glycoprotein (Pgp) and CD243. A 170-kDa transmembrane protein, MDR-1 is an ATP-dependent efflux pump for lipophilic compounds, including anti-cancer drugs. Expression of MDR-1 has been shown to correlate with multidrug resistance. In fact, tumor resistance to chemotherapy has been linked to MDR-1 expression in many cancers. MDR-1 is expressed in a variety of tissues, including the brain, kidney, liver, pancreas, and testes. Within the immune system, this molecule can be found on normal T, B, and natural killer cells, but not on monocytes.

This antibody has been reported to inhibit MDR1-mediated efflux.


Applications Reported: This UIC2 antibody has been reported for use in flow cytometric analysis.

Applications Tested: This UIC2 antibody has been pre-titrated and tested by flow cytometric analysis on multidrug resistant cell lines. This can be used at 5 µL (0.5 µg) per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10<sup>5</sup> to 10<sup>8</sup> cells/test.

Excitation: 488 nm; Emission: 520 nm; Laser: Blue Laser.

Filtration: 0.2 µm post-manufacturing filtered.

## Product Images For CD243 (ABCB1) Monoclonal Antibody (UIC2), FITC, eBioscience™



### CD243 (ABCB1) Antibody (11-2439-42) in Flow

Staining of the 8226/S (left) and 8226 DOX40 (right) cell lines with Mouse IgG2a K Isotype Control FITC (Product # 11-4724-42) (blue histogram) or Anti-Human CD243 (ABCB1) PE (purple histogram). Total viable cells were used for analysis.

## 1 Reference

### Flow Cytometry (1)

Stem cells international

#### Optimized Stem Cell Detection Using the DyeCycle-Triggered Side Population Phenotype.

"Published figure using CD243 (ABCB1) monoclonal antibody (Product # 11-2439-42) in Flow Cytometry"

Authors: Boesch M, Wolf D, Sopper S

**Species**  
Human

**Dilution**  
Not Cited

**Year**  
2016

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.