

Mouse IgG1 kappa Isotype Control (P3.6.2.8.1), FITC, eBioscience™

Product Details

Size	50 µg
Host/Isotype	Mouse / IgG1, kappa
Class	Control
Type	Isotype Control
Clone	P3.6.2.8.1
Conjugate	FITC
Excitation/Emission Max	498/517 nm
Form	Liquid
Concentration	0.5 mg/mL
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2
Contains	0.09% sodium azide
Storage conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_470021

Applications	Tested Dilution	Publications
Immunohistochemistry (IHC)	Assay-Dependent	-
Immunocytochemistry (ICC/IF)	Assay-Dependent	0 Publication
Flow Cytometry (Flow)	Assay-Dependent	0 Publication
Control (Ctrl)	Assay-Dependent	0 Publication

Product Specific Information


Description: The monoclonal mouse IgG1 K immunoglobulin is useful as an isotype control.

Applications Reported: FITC Mouse IgG1 K Isotype Control has been reported for use in immunocytochemistry, immunohistochemistry, and flow cytometric analysis.

Applications Tested: This Mouse IgG1 K Isotype Control can be used at the same concentration as the experimental antibody.


Excitation: 488 nm; **Emission:** 520 nm; **Laser:** Blue Laser.

Filtration: 0.2 µm post-manufacturing filtered.



Mouse IgG1 kappa Isotype Control (11-4714-81) in Flow

C57BL/6 mouse splenocytes were stained intracellularly, using the Foxp3 /Transcription Factor Staining Buffer Set (Product # 00-5523-00) and protocol, with 1.0 µg of Mouse IgG1 kappa Isotype Control, PE (Product # 11-4714-82) (blue histogram) or 1.0 µg of ID2 Monoclonal Antibody, PE (purple histogram). Splenocytes within the lymphocyte gate positive for NK1.1 Monoclonal Antibody, APC (Product # 17-5941-82) and CD49b Monoclonal Antibody, APC (Product # 17-5971-82) were used for analysis.



Mouse IgG1 kappa Isotype Control (11-4714-81) in Flow

Normal human peripheral blood cells were stimulated for 4 hours with LPS (Product # 00-4976-03) in the presence of Brefeldin A (Product # 00-4506-51). Cells were then surface stained with CD14 Monoclonal Antibody, APC (Product # 17-0149-42), followed by intracellular staining using the Intracellular Fixation & Permeabilization Buffer Set (Product # 88-8824-00) and protocol, with and Mouse IgG1 kappa Isotype Control, FITC (Product # 11-4714-82) (left) or CRM56 Monoclonal Antibody, FITC (right). Cells in the monocyte gate were used for analysis.

Mouse IgG1 kappa Isotype Control (11-4714-81) in Flow

Normal human peripheral blood cells were stained with CD11b Monoclonal Antibody, APC (Product # 17-0118-42) and Mouse IgG1 kappa Isotype Control, FITC (Product # 11-4714-82) (left) or CD85j Monoclonal Antibody, FITC (right). Cells in the monocyte gate were used for analysis.

[View more figures on thermofisher.com](https://thermofisher.com)

81 References

3D printed PLGA/MgO/PDA composite scaffold by low-temperature deposition manufacturing for bone tissue engineering applications. Regen Ther (2023)

STING signaling activation modulates macrophage polarization via CCL2 in radiation-induced lung injury. J Transl Med (2023)

Molecular basis for nuclear accumulation and targeting of the inhibitor of apoptosis BIRC2. Nat Struct Mol Biol (2023)

Irreversible HER2 inhibitors overcome resistance to the RSL3 ferroptosis inducer in non-HER2 amplified luminal breast cancer. Cell Death Dis (2023)

The regulatory effect of the YY1/miRHCC2/BAMBI axis on the stemness of liver cancer cells. Int J Oncol (2023)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (i) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (ii) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (iii) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (iv) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.