

Mouse IgG2a kappa Isotype Control (eBM2a), FITC, eBioscience™

Product Details

Size	50 µg
Published Species	Mouse, Human
Host/Isotope	Mouse / IgG2a, kappa
Class	Control
Type	Isotype Control
Clone	eBM2a
Conjugate	FITC
Form	Liquid
Concentration	0.5 mg/mL
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2, with 0.1% gelatin
Contains	0.09% sodium azide
Storage Conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_470027

Applications	Tested Dilution	Publications
Control (Ctrl)	Assay-Dependent	2 Publications
Flow Cytometry (Flow)	Assay-Dependent	4 Publications
Immunocytochemistry (ICC)	Assay-Dependent	-
Immunofluorescence (IF)	Assay-Dependent	-
Immunohistochemistry (IHC)	Assay-Dependent	-

Product Specific Information

Description: This is a monoclonal mouse IgG2a, kappa antibody. It is used as an isotype control for mouse IgG2a antibodies.

Applications Reported: This mouse IgG2a isotype control has been reported for use in cell surface and intracellular flow cytometric analysis, immunocytochemistry, and immunohistochemistry.

Applications Tested: The FITC conjugated mouse IgG2a isotype control has been tested by flow cytometric analysis of normal human peripheral blood cells and should be used at the same concentration as the experimental antibody.

Excitation: 488 nm; **Emission:** 520 nm; **Laser:** Blue Laser.

Filtration: 0.2 µm post-manufacturing filtered.

Flow Cytometry (4)

PloS one

Splenic Leukocytes Traffic to the Thyroid and Produce a Novel TSH Isoform during Acute *Listeria monocytogenes* Infection in Mice.

"11-4724 was used in Flow cytometry/Cell sorting to show that within three days of systemic infection of mice with *Listeria monocytogenes*, splenic leukocytes synthesized elevated levels of TSHv."

Authors: Montufar-Solis D, Klein JR

Species
Mouse

Dilution
Not Cited

Year
2016

Oncotarget

Anti-angiogenic efficacy of 5'-triphosphate siRNA combining VEGF silencing and RIG-I activation in NSCLCs.

"11-4724 was used in Flow cytometry/Cell sorting to demonstrate a novel siRNA molecule could successfully knock down VEGF and assess its antitumor potential."

Authors: Yuan D, Xia M, Meng G, Xu C, Song Y, Wei J

Species
Human

Dilution
Not Cited

Year
2015

[View more Flow references on thermofisher.com](#)

Control (2)

Journal of immunology (Baltimore, Md. : 1950)

Dendritic cell-specific ablation of the protein tyrosine phosphatase Shp1 promotes Th1 cell differentiation and induces autoimmunity.

"11-4724 was used as a Control in experiments to investigate the molecules that regulate dendritic cells to protect against autoimmunity, showing that loss of Shp1 promotes Th1 cell differentiation and induces autoimmunity."

Authors: Kaneko T, Saito Y, Kotani T, Okazawa H, Iwamura H, Sato-Hashimoto M, Kanazawa Y, Takahashi S, Hiromura K, Kusakari S, Kaneko Y, Murata Y, Ohnishi H, Nojima Y, Takagishi K, Matozaki T

Species
Mouse

Dilution
Not Cited

Year
2012

BMC musculoskeletal disorders

TRAIL death receptor-4, decoy receptor-1 and decoy receptor-2 expression on CD8+ T cells correlate with the disease severity in patients with rheumatoid arthritis.

"11-4724 was used as a Control in experiments to detect CD8+ T Cell expression of TRAIL Death Receptor-4, Decoy Receptor-1 and Decoy Receptor-2 from patients with Rheumatoid Arthritis, implicated in their disease severity."

Authors: Bisgin A, Terzioglu E, Aydin C, Yoldas B, Yazisiz V, Balci N, Bagci H, Gorczynski RM, Akdis CA, Sanlioglu S

Species
Human
Not Applicable

Dilution
Not Cited
Not Cited

Year
2010

More applications with references on thermofisher.com

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.