

CD11c Monoclonal Antibody (N418), PE, eBioscience™

Product Details

Size	100 µg
Species Reactivity	Mouse
Published Species	Mouse, Human
Host/Isotype	Armenian hamster / IgG
Recommended Isotype Control	Armenian Hamster IgG Isotype Control (eBio299Arm), PE, eBioscience™
Class	Monoclonal
Type	Antibody
Clone	N418
Conjugate	PE
Excitation/Emission Max	565/576 nm
Form	Liquid
Concentration	0.2 mg/mL
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2
Contains	0.09% sodium azide
Storage conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_465552

Applications	Tested Dilution	Publications
Immunohistochemistry (IHC)	-	3 Publications
Immunohistochemistry (Frozen) (IHC (F))	-	5 Publications
Immunocytochemistry (ICC/IF)	-	3 Publications
Flow Cytometry (Flow)	0.5 µg/test	247 Publications
ELISA (ELISA)	-	1 Publication
Functional Assay (FN)	-	1 Publication

Product Specific Information

Description: The N418 monoclonal antibody reacts with mouse CD11c, the integrin alphaX. CD11c non-covalently associates with beta2 integrin to form the CD11c/CD18 heterodimer. CD11c is expressed by dendritic cells, a subset of Intestinal Intraepithelial Lymphocytes (IEL) and some activated T cells. CD11c/CD18 binds to CD54, iC3b and fibrinogen and plays a role in leukocyte adhesive interactions. N418 binds to CD11c on splenic dendritic cells in the T-dependent areas of mouse spleen and precipitates a 150, 90 kDa heterodimer.


Applications Reported: The N418 antibody has been reported for use in flow cytometric analysis.

Applications Tested: The N418 antibody has been tested by flow cytometric analysis of mouse splenocytes. This can be used at less than or equal to 0.5 µg per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10⁵ to 10⁸ cells/test. It is recommended that the antibody be carefully titrated for optimal performance in the assay of interest.

Excitation: 488-561 nm; Emission: 578 nm; Laser: Blue Laser, Green Laser, Yellow-Green Laser.

Filtration: 0.2 µm post-manufacturing filtered.

Product Images For CD11c Monoclonal Antibody (N418), PE, eBioscience™



CD11c Antibody (12-0114-82) in Flow
Staining of C57BL/6 splenocytes with Anti-Human/Mouse CD45R (B220) APC (Product # 17-0452-82) and 0.25 µg of Armenian Hamster IgG Isotype Control PE (Product # 12-4888-81) (left) or 0.25 µg of Anti-Mouse CD11c PE (right). Total viable cells were used for analysis.

View more figures on thermofisher.com

Immunohistochemistry (3)

<p>Clinical and experimental immunology</p> <p>IL-1-dependent electrophysiological changes and cardiac neural remodeling in a mouse model of Kawasaki disease vasculitis.</p> <p>"12-0114 was used in Immunohistochemistry to show that these ECG changes are recapitulated in the Lactobacillus casei cell wall extract (LCWE)-induced KD vasculitis mouse model."</p> <p>Authors: Abe M,Rastelli DD,Gomez AC,Cingolani E, Lee Y,Soni PR,Fishbein MC,Lehman TJA,Shimada K,Crother TR, Chen S,Noval Rivas M,Arditi M</p>	<p>Year 2020</p> <p>Species Mouse</p>
<p>Journal of visualized experiments : JoVE</p> <p>Precision-cut Mouse Lung Slices to Visualize Live Pulmonary Dendritic Cells.</p> <p>"12-0114 was used in in vivo experiments to contribute to a comprehensive understanding of cellular events that underlie allergic and inflammatory diseases of the lung."</p> <p>Authors: Lyons-Cohen MR,Thomas SY,Cook DN,Nakano H</p>	<p>Year 2017</p> <p>Species Mouse</p>

View more IHC references on thermofisher.com

Immunohistochemistry (Frozen) (5)

<p>JCI insight</p> <p>Heterogeneous fibroblasts underlie age-dependent tertiary lymphoid tissues in the kidney.</p> <p>"12-0114 was used in Immunofluorescence to show how the inhibition of tertiary lymphoid tissue may constitute a therapeutic approach for treating acute kidney injury in the elderly."</p> <p>Authors: Sato Y,Mii A,Hamazaki Y,Fujita H,Nakata H,Masuda K,Nishiyama S,Shibuya S,Haga H,Ogawa O,Shimizu A, Narumiya S,Kaisho T,Arita M,Yanagisawa M,Miyasaka M,Sharma K,Minato N,Kawamoto H,Yanagita M</p>	<p>Year 2016</p> <p>Species Mouse</p>
<p>Journal of immunology (Baltimore, Md. : 1950)</p> <p>A TNF--CCL20-CCR6 axis regulates Nod1-induced B cell responses.</p> <p>"12-0114 was used in Flow cytometry/Cell sorting to reveal a novel mechanism of B cells during inflammation and shed light on how B cells participate in innate immune responses to microbial stimulation."</p> <p>Authors: Paradis M,Mindt BC,Duerr CU,Rojas OL,Ng D,Boulianne B,McCarthy DD,Yu MD,Summers deLuca LE,Ward LA,Waldron JB,Philpott DJ,Gommerman JL,Fritz JH</p>	<p>Year 2014</p> <p>Species Mouse</p>

View more IHC (F) references on thermofisher.com

More applications with references on thermofisher.com

- ICC/IF (3)
- Flow (247)
- ELISA (1)
- FN (1)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.