

# CD36 Monoclonal Antibody (HM36), PE, eBioscience™

Product Details	
Size	100 µg
Species Reactivity	Mouse
Host/Isotype	Armenian hamster / IgG
Recommended Isotype Control	Armenian Hamster IgG Isotype Control (eBio299Arm), PE, eBioscience™
Class	Monoclonal
Type	Antibody
Clone	HM36
Conjugate	PE
Excitation/Emission Max	565/576 nm
Immunogen	CHO cells transfected with full-length mouse CD36
Form	Liquid
Concentration	0.2 mg/mL
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2
Contains	0.09% sodium azide
Storage conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_2734969

Applications	Tested Dilution	Publications
Flow Cytometry (Flow)	0.5 µg/test	1 Publication


## Product Specific Information

**Description:** This HM36 antibody recognizes mouse CD36, also known as scavenger receptor BIII.

**Applications Reported:** This HM36 antibody has been reported for use in flow cytometric analysis.


**Applications Tested:** This HM36 antibody has been tested by flow cytometric analysis of thioglycolate-elicited peritoneal macrophages. This may be used at less than or equal to 0.5 µg per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10<sup>5</sup> to 10<sup>8</sup> cells/test. It is recommended that the antibody be carefully titrated for optimal performance in the assay of interest.

**Excitation:** 488-561 nm; **Emission:** 578 nm; **Laser:** Blue Laser, Green Laser, Yellow-Green Laser




**CD36 Antibody (12-0362-82)**

Staining of mouse resident peritoneal exudate cells. As expected based on known expression patterns, CD36 is expressed on Small Peritoneal Macrophages (SPM) and Large Peritoneal Macrophages (LPM) but not eosinophils or lymphocytes. Details: C57BL/6 resident peritoneal exudate cells were stained with CD11b (clone M1/70), F4/80 (clone BM8), and either CD36 (clone HM36, colored histograms), or Armenian Hamster IgG Isotype Control (gray histograms). Cells in the indicated color gates were used for analysis. {RE}



**CD36 Antibody (12-0362-82) in Flow**

BALB/c mouse thioglycolate-elicited peritoneal exudate cells were stained with F4/80 Monoclonal Antibody, FITC (Product # 11-4801-82) and 0.25 µg of Armenian Hamster IgG Isotype Control, PE (Product # 12-4888-81) (left) or 0.25 µg of CD36 Monoclonal Antibody, PE (right).



**CD36 Antibody (12-0362-82)**

Staining of RAW264.7 cells treated with IL-4. As expected based on the published data, RAW264.7 polarized with IL-4 for 24 hours up-regulate expression of CD36. Details: RAW264.7 cells were cultured untreated (purple histogram) or treated with IL-4 for 24 hours (orange histogram). The cells were then Fc blocked and stained with CD36 (clone HM36) (orange and purple histograms) or Armenian Hamster Isotype control (blue histogram). {TM}

[View more figures on thermofisher.com](https://thermofisher.com)

Flow Cytometry (1)

PLoS pathogens	Year 2021
<b>Carbomer-based adjuvant elicits CD8 T-cell immunity by inducing a distinct metabolic state in cross-presenting dendritic cells.</b>	
"Published figure using CD36 monoclonal antibody (Product # 12-0362-82) in Flow Cytometry"	
Authors: Lee W,Kingstad-Bakke B,Paulson B,Larsen A,Overmyer K,Marinaik CB,Dulli K,Toy R,Vogel G,Mueller KP, Tweed K,Walsh AJ,Russell J,Saha K,Reyes L,Skala MC,Sauer JD,Shayakhmetov DM,Coon J,Roy K,Suresh M	

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.