

CD40 Monoclonal Antibody (1C10), PE, eBioscience™

Product Details	
Size	100 µg
Species Reactivity	Mouse
Published Species	Mouse, Human
Host/Isotype	Rat / IgG2a, kappa
Recommended Isotype Control	Rat IgG2a kappa Isotype Control (eBR2a), PE, eBioscience™
Class	Monoclonal
Type	Antibody
Clone	1C10
Conjugate	PE
Form	Liquid
Concentration	0.2 mg/mL
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2
Contains	0.09% sodium azide
Storage conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_465649

Applications	Tested Dilution	Publications
Flow Cytometry (Flow)	0.5 µg/test	64 Publications
Neutralization (Neu)	-	1 Publication
Inhibition Assays (IA)	-	1 Publication

Product Specific Information

Description: The 1C10 monoclonal antibody reacts with mouse CD40, a 45-50 kDa type I transmembrane glycoprotein. CD40 is a member of the TNFR family and is expressed by mouse B lymphocytes, follicular dendritic cells, thymic epithelium, and a subset of peripheral T cells. CD40 regulates B cell development/maturation by inducing Ig isotype switching and in combination with other signals such as IL-4, protects B cells from surface Ig-induced apoptosis and promotes proliferation. Interaction of CD40 with CD154 (gp39), its ligand on T cells, is important in T-B cell crosstalk and plays a role in costimulation and immune regulation.

The monoclonal antibody 1C10 is reported to be agonistic in vitro and in vivo.


Applications Reported: The 1C10 antibody has been reported for use in flow cytometric analysis.

Applications Tested: The 1C10 antibody has been tested by flow cytometric analysis of mouse splenocytes. This can be used at less than or equal to 0.5 µg per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10⁵ to 10⁸ cells/test. It is recommended that the antibody be carefully titrated for optimal performance in the assay of interest.

Excitation: 488-561 nm; Emission: 578 nm; Laser: Blue Laser, Green Laser, Yellow-Green Laser.

Filtration: 0.2 µm post-manufacturing filtered.

Product Images For CD40 Monoclonal Antibody (1C10), PE, eBioscience™



CD40 Antibody (12-0401-82) in Flow

Staining of BALB/c splenocytes with Anti-Mouse CD19 FITC (Product # 11-0193-82) and 0.25 µg of Rat IgG2a K Isotype Control PE (Product # 12-4321-80) (left) or 0.25 µg of Anti-Mouse CD40 PE (right). Total viable cells were used for analysis.

[View more figures on thermofisher.com](http://thermofisher.com)

Flow Cytometry (64)

Journal for immunotherapy of cancer

Modulation of lactate-lysosome axis in dendritic cells by clotrimazole potentiates antitumor immunity.

"12-0401-82 was used in Flow Cytometry to show that clotrimazole could trigger DC activation via the lactate-lysosome axis to promote antigen cross-presentation and could be used as a potential combination therapy approach to improving the therapeutic efficacy of anti-PD1 immunotherapy."

Authors: Wang Z,Xu F,Hu J,Zhang H,Cui L,Lu W,He W,Wang X,Li M,Zhang H,Xiong W,Xie C,Liu Y,Zhou P,Liu J,Huang P,Qin XF,Xia X

Species
Mouse

Dilution
Not Cited

Year
2021

International journal of molecular medicine

Prostaglandin E2 serves a dual role in regulating the migration of dendritic cells.

"12-0401 was used in Flow cytometry/Cell sorting to elucidate the potential regulatory mechanism of PGE2 on the migration of dendritic cells."

Authors: Diao G,Huang J,Zheng X,Sun X,Tian M,Han J,Guo J

Species
Mouse

Dilution
1:100

Year
2021

[View more Flow references on thermofisher.com](#)

Neutralization (1)

PloS one

Retinal astrocytes pretreated with NOD2 and TLR2 ligands activate uveitogenic T cells.

"12-0401 was used in Flow cytometry/Cell sorting to investigate the activation of uveitogenic T cells via the pretreatment of retinal astrocytes with NOD2 and TLR2 ligands."

Authors: Jiang G,Sun D,Kaplan HJ,Shao H

Species
Mouse

Dilution
Not Cited

Year
2013

Inhibition Assays (1)

PloS one

Retinal astrocytes pretreated with NOD2 and TLR2 ligands activate uveitogenic T cells.

"12-0401 was used in Flow cytometry/Cell sorting to investigate the activation of uveitogenic T cells via the pretreatment of retinal astrocytes with NOD2 and TLR2 ligands."

Authors: Jiang G,Sun D,Kaplan HJ,Shao H

Species
Mouse

Dilution
Not Cited

Year
2013

More applications with references on thermofisher.com

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.