

# CD195 (CCR5) Monoclonal Antibody (eBioT21/8 (T21/8)), PE, eBioscience™

Product Details	
Size	100 Tests
Species Reactivity	Human
Host/Isotype	Mouse / IgG1, kappa
Recommended Isotype Control	Mouse IgG1 kappa Isotype Control (P3.6.2.8.1), PE, eBioscience™
Class	Monoclonal
Type	Antibody
Clone	eBioT21/8 (T21/8)
Conjugate	PE
Excitation/Emission Max	565/576 nm
Form	Liquid
Concentration	5 µL/Test
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2, with 0.2% BSA
Contains	0.09% sodium azide
Storage conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_10853667

Applications	Tested Dilution	Publications
Flow Cytometry (Flow)	5 µL (0.125 µg)/test	-

## Product Specific Information

**Description:** The eBioT21/8 monoclonal antibody reacts with the amino terminus of human CCR5 (CD195), an approximately 45 kDa member of the G protein-coupled receptor (GPCR) superfamily that binds chemokines including MIP-1alpha, MIP-1beta and RANTES. Human CCR5 is expressed on resting T cells with a memory/effector phenotype, monocytes, macrophages and immature dendritic cells. CCR5 functions as a receptor to direct the chemotaxis of lymphocytes, and is the primary co-receptor for macrophage-tropic Human Immunodeficiency Virus Type 1 (HIV-1), which binds CCR5 through gp120. Binding of the eBioT21/8 monoclonal antibody displays donor variability and may be affected by sub-optimal staining conditions.


**Applications Reported:** This eBioT21/8 (T21/8) antibody has been reported for use in flow cytometric analysis.

**Applications Tested:** This eBioT21/8 (T21/8) antibody has been pre-titrated and tested by flow cytometric analysis of normal human peripheral blood cells. For optimal performance, it is recommended that staining with eBioT21/8 be done at room temperature or 37°C for 1 hour in Flow Cytometry Staining Buffer (cat. 00-4222). This can be used at 5 µL (0.125 µg) per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10<sup>5</sup> to 10<sup>8</sup> cells/test.

**Excitation:** 488-561 nm; **Emission:** 578 nm; **Laser:** Blue Laser, Green Laser, Yellow-Green Laser.

**Filtration:** 0.2 µm post-manufacturing filtered.

Product Images For CD195 (CCR5) Monoclonal Antibody (eBioT21/8 (T21/8)), PE, eBioscience™



**CD195 (CCR5) Antibody (12-1957-42) in Flow**  
Staining of normal human peripheral blood cells with Anti-Human CD3 APC (Product # 17-0038-42) and Mouse IgG1 kappa Isotype Control PE (Product # 12-4714-81) (left) or Anti-Human CD195 (CCR5) PE (right). Cells in the lymphocyte gate were used for analysis.

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.