

IL-1 alpha Monoclonal Antibody (ALF-161), PE, eBioscience™

Product Details	
Size	100 µg
Species Reactivity	Mouse
Published Species	Mouse
Host/Isotope	Armenian hamster / IgG
Recommended Isotype Control	Armenian Hamster IgG Isotype Control (eBio299Arm), PE, eBioscience™
Class	Monoclonal
Type	Antibody
Clone	ALF-161
Conjugate	PE
Form	Liquid
Concentration	0.2 mg/mL
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2, with 0.1% gelatin
Contains	0.09% sodium azide
Storage Conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_466144

Applications	Tested	Dilution	Published
Flow Cytometry (Flow)	✓	0.5 µg/test	1 Publication

Product Specific Information

Description: The ALF-161 antibody reacts with mouse interleukin-1alpha (IL-1alpha). Mouse IL-1alpha, also called Lymphocyte Activating Factor (LAF), Endogenous Pyrogen (EP), Leukocyte Endogenous Mediator (LEM), and Mononuclear Cell Factor (MCF), is a 17 kDa factor produced by a wide variety of cells, including macrophages, dendritic cells, T and B cells. IL-1alpha is mostly cell-associated, with 23% amino acid homology with IL-1beta. The immune regulatory role of IL-1alpha is exerted on a wide range of cells including lymphocytes, epithelial cells and fibroblasts. In vivo, it induces hypotension, fever, and acute phase response.

Applications Reported: The ALF-161 antibody has been reported for use in ELISA capture, ELISPOT capture, neutralization, and intracellular staining for flow cytometry.

Applications Tested: This ALF-161 antibody is offered in 2 formats:


- µg size: Can be used at less than or equal to 0.5 µg per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10⁵ to 10⁸ cells/test. It is recommended that the antibody be carefully titrated for optimal performance in the assay of interest.

- test size: has been pre-titrated can be used at test size: 5 µL (0.25µg) per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10⁵ to 10⁸ cells/test.

Excitation: 488-561 nm; Emission: 578 nm; Laser: Blue Laser, Green Laser, Yellow-Green Laser.

Filtration: 0.2 µm post-manufacturing filtered.

Product Images For IL-1 alpha Monoclonal Antibody (ALF-161), PE, eBioscience™



IL-1 alpha Antibody (12-7011-82) in Flow

Mouse thioglycolate-induced peritoneal exudate cells were stimulated with LPS in the presence of Brefeldin A for 22 hours. The cells were surface stained with Anti-Mouse CD11b FITC (Product # 11-0112-41) and intracellularly stained with Rat IgG2b kappa Isotype Control PE (Product # 12-4031-82) (left) or with Anti-Mouse IL-1 alpha PE (right).

1 Reference

Flow Cytometry (1)

Journal of immunology (Baltimore, Md. : 1950)

IL-1 and IL-1 recruit different myeloid cells and promote different stages of sterile inflammation.

Authors: Rider P, Carmi Y, Guttman O, Braiman A, Cohen I, Voronov E, White MR, Dinarello CA, Apte RN

Species
Mouse

Dilution
Not Cited

Year
2011

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.