

CD282 (TLR2) Monoclonal Antibody (TL2.1), PE, eBioscience™

Product Details

Size	100 Tests
Species Reactivity	Human
Published Species	Human, Mouse
Host/Isotype	Mouse / IgG2a, kappa
Recommended Isotype Control	Mouse IgG2a kappa Isotype Control (eBM2a), PE, eBioscience™
Class	Monoclonal
Type	Antibody
Clone	TL2.1
Conjugate	PE
Excitation/Emission Max	565/576 nm
Form	Liquid
Concentration	5 µL/Test
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2, with 0.2% BSA
Contains	0.09% sodium azide
Storage conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_10667887

Applications	Tested Dilution	Publications
Immunohistochemistry (Paraffin) (IHC (P))	-	2 Publications
Immunohistochemistry (Frozen) (IHC (F))	-	1 Publication
Immunocytochemistry (ICC/IF)	-	1 Publication
Flow Cytometry (Flow)	5 µL (1 µg)/test	35 Publications
Functional Assay (FN)	-	6 Publications
Miscellaneous PubMed (Misc)	-	1 Publication

Product Specific Information

Description: The TL2.1 monoclonal antibody reacts with human Toll-like receptor 2 (TLR2). To date, at least ten members of the Toll family have been identified in human. This family of type I transmembrane proteins is characterized by an extracellular domain with leucine-rich repeats and a cytoplasmic domain with homology to the type I IL-1 receptor. Two of these receptors, TLR2 and TLR4, are pattern recognition receptors and signaling molecules in response to bacterial lipoproteins and have been implicated in innate immunity and inflammation. TLR2 is expressed by peripheral blood monocytes and is responsible for distinguishing different pathogens. TL2.1, a blocking antibody, has been used to study the role of TLR-2 as a pattern recognition receptor in microbial lipoprotein/lipopeptide induced cytokine production from human peripheral blood mononuclear cells. TL2.1 has been reported to immunoprecipitate human TLR2 (~90 kDa) from PBMC and HMEC.

Applications Reported: The TL2.1 antibody has been reported for use in flow cytometric analysis.


Applications Tested: This TL2.1 antibody has been pre-titrated and tested by flow cytometric analysis of normal human peripheral blood cells. This can be used at 5 µL (1 µg) per test. A test is defined as the amount (µg) of antibody that will stain a

cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10⁵ to 10⁸ cells /test.

Excitation: 488-561 nm; Emission: 578 nm; Laser: Blue Laser, Green Laser, Yellow-Green Laser.

Filtration: 0.2 µm post-manufacturing filtered.

Product Images For CD282 (TLR2) Monoclonal Antibody (TL2.1), PE, eBioscience™



CD282 (TLR2) Antibody (12-9922-42) in Flow
Staining of normal human peripheral blood cells with 2 µg of Mouse IgG2a K Isotype Control PE (Product # 12-4724-81) (open histogram) or Anti-Human CD282 (TLR2) PE (filled histogram). Cells in the monocyte gate were used for analysis.

[View more figures on thermofisher.com](#)

Immunohistochemistry (Paraffin) (2)

Oral microbiology and immunology	Year 2003
Immunohistochemical localization of Toll-like receptors 2 and 4 in gingival tissue from patients with periodontitis.	
Authors: Mori Y,Yoshimura A,Ukai T,Lien E,Espevik T,Hara Y	
Histochemistry and cell biology	Year 2003
Toll-like receptor 2 is expressed by alveolar epithelial cells type II and macrophages in the human lung.	
Authors: Droemann D,Goldmann T,Branscheid D,Clark R,Dalhoff K,Zabel P,Vollmer E	

Immunohistochemistry (Frozen) (1)

Journal of immunology (Baltimore, Md. : 1950)	Year 2004
Intracellularly expressed TLR2s and TLR4s contribution to an immunosilent environment at the ocular mucosal epithelium.	
Authors: Ueta M,Nochi T,Jang MH,Park EJ,Igarashi O,Hino A,Kawasaki S,Shikina T,Hiroi T,Kinoshita S,Kiyono H	

Immunocytochemistry (1)

Veterinary immunology and immunopathology	Year 2008
Antibodies specific for human or murine Toll-like receptors detect canine leukocytes by flow cytometry.	
Authors: Burgener IA,Jungi TW	

More applications with references on thermofisher.com

- Flow (35)
- FN (6)
- Misc (1)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (i) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (ii) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (iii) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (iv) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.